


Aluminum Cylinders LED

6" Aluminum Cylinders LED

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5641-20/30K	Bronze	One-light down 	6" W., 12" ht.	1 29w integrated LED,
P5641-30/30K	White		Extends 8-7/8".	3000K, 90CRI,
P5641-31/30K	Black		H/CTR 4-1/2".	1800 delivered lumens
P5641-82/30K	Metallic Gray			
P5642-20/30K	Bronze	Two-light up/down For wet location requires top cover lens, P860046	6" W., 18" ht.	2 29w integrated LED,
P5642-30/30K	White		Extends 8-7/8".	3000K, 90CRI,
P5642-31/30K	Black		H/CTR 8".	2566 delivered lumens
P5642-82/30K	Metallic Gray			
P5741-20/30K	Bronze	One-light cylinder. Mounts flush to ceiling or hangs with pendant accessory kit	6" W., 12" ht.	1 29w integrated LED,
P5741-30/30K	White		3000K, 90CRI,	
P5741-31/30K	Black		1800 delivered lumens	
P5741-82/30K	Metallic Gray			

All fixtures:



P5641-20/30K



P5641-30/30K



P5641-31/30K



P5641-82/30K



P5642-20/30K



P5642-30/30K



P5642-31/30K



P5642-82/30K



P5741-20/30K



P5741-30/30K



P5741-31/30K




P5741-82/30K

Aluminum Cylinders

Sleek, cylindrical forms in elegant finish selections. Die-cast aluminum wall brackets and heavy-duty aluminum framing. Fade and chip-resistant. UL listed for wet locations when used with lens cover. Dark Sky compliant for down light only.

5" Aluminum Cylinders

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5674-20	Bronze	One-light down 	5" W., 7-1/4" ht.	1 75w PAR-30
P5674-30	White		Extends 8".	or 75w BR-30
P5674-31	Black		H/CTR 2-1/2".	
P5674-82	Metallic Gray			
P5675-20	Bronze	Two-light up/down For wet locations requires top cover lens, P860045	5" W., 14" ht.	2 75w PAR-30
P5675-30	White		Extends 8".	
P5675-31	Black		H/CTR 7".	
P5675-82	Metallic Gray			
P5774-20	Bronze	One-light. Mounts flush to ceiling	5" dia., 6-3/4" ht.	1 75w PAR-30 or 75w BR-30
P5774-30	White			
P5774-31	Black			



P5675-20



P5675-82



P5774-20



P5774-30



P5774-31



P5674-31



P5674-20



P5674-82

6" Aluminum Cylinders

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5641-20	Bronze	One-light down	6" W., 12" ht.	1 250w PAR-38
P5641-30	White		Extends 8-7/8".	or 150w BR-40
P5641-31	Black		H/CTR 4-1/2".	
P5641-82	Metallic Gray			
P5642-20	Bronze	Two-light up/down. For wet location requires top cover lens, P860046	6" W., 18" ht.	2 250w PAR-38
P5642-30	White		Extends 8-7/8".	or 150w BR-40
P5642-31	Black		H/CTR 8".	
P5642-82	Metallic Gray			
P5741-20	Bronze	One-light cylinder. Mounts flush to ceiling or hangs with pendant accessory kit	6" dia., 12" ht.	1 250w PAR-38 or 150w BR-40
P5741-30	White			
P5741-31	Black			



P5741-30



P5741-31



P5641-31



P5641-82



P5642-20