

# Remotes, Wall Controls & 45° Canopies



**P2662-01**  
Fan/Light Remote  
Universal remote operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four “dip” switches and 16 code options to avoid the chance of interference from other remotes.



**P2663-01**  
Fan/Light Remote  
Universal remote with two, four or eight-hour timer option, operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring many code combination options to avoid the chance of interference from other remotes.



**P2618-01**  
Fan/Light Remote  
Provides fan speed and light control from convenient hand-held remote. Compatible with non-dimmable compact fluorescent lamps. For single pole applications. Receiver fits in fan canopy.



**P2661-01**  
Universal Fan/Light Remote  
Provides fan speed and full range light dimming control from a convenient hand held remote control. For single pole applications. Includes a wall plate for added storage convenience. Receiver fits in the fan canopy.



**P2667-031**  
Wifi Fan/Light Remote  
Universal Wifi remote control for AC motor fans. Control your ceiling fan or light kit via Wifi from anywhere. Pairs with Alexa, Google Home, or app on your phone or tablet. Voice control the fan with three speeds and the light with full range dimming. App control the fan with three speeds or four timer selections or full range dimming control of the light. Can be controlled with the hand held remote included with the kit.



**P2665-30** White  
Universal remote includes a wall mount transmitter, ideal for multi-family applications, that operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four “dip” switches and 16 code options to avoid the chance of interference from other remotes.



**P2631-30** White  
Full-function wall control transmitter (receiver sold with ceiling fan). Use with, or in place of, hand-held remote included with fans that have a downlight. Includes switch plate cover.



**P2630-95** Ivory  
Four-speed fan wall control with full-range light dimmer. Fits single-gang wall box; requires two circuits. Includes switch plate cover. Not for use with multiple fans.



**P2630-30** White  
Four-speed fan wall control with full-range light dimmer. Fits single-gang wall box; requires two circuits. Includes switch plate cover. Not for use with multiple fans.



**P2613-95** Ivory  
Four-speed fan wall control. Includes switch plate cover. Not for use with multiple fans.



**P2613-30** White  
Four-speed fan wall control. Includes switch plate cover. Not for use with multiple fans.



**P2666-09**  
Brushed Nickel  
45° canopy



**P2666-30**  
White  
45° canopy



**P2666-129**  
Architectural Bronze  
45° canopy