



Everlume™ Square Surface Mount LED

Edgelit technology creates a large glare free and evenly illuminated surface for a variety of applications for both residential and commercial applications. Offering a low profile design, LED Everlume™ Square Surface Mount is available in three sizes: 7", 11", and 14", in a White finish. The integrated driver does not recess into junction box, allowing for easy installation into 4" octagonal, 4" round PVC and 4" x 1/2" ceiling pan junction boxes. Wet location listed and offers a 50,000-hour LED life.



LED FEATURES

- Wet location listed.
- 120v input voltage.
- Flicker-free dimming with many Triac and ELV dimmers.
- 50,000 hour life.

7" SQUARE

P810019-030-30 White
7" sq., 1-1/8" ht.
15w integrated LED,
3000, 90CRI, 1100 lumens.



P810019-030-30



P810020-030-30

11" SQUARE

P810020-030-30 White
11" sq., 1-1/8" ht.
17w integrated LED,
3000, 90CRI, 1400 lumens.

14" SQUARE

P810021-030-30 White
14" sq., 1-1/8" ht.
20w integrated LED,
3000, 90CRI, 1600 lumens.



P810021-030-30

Everlume™ Square Trim Accessories

Design the perfect lighting aesthetic for any residential or commercial setting with our Everlume™ Square Trim Accessories collection. We offer a variety of finishes and square trim sizes to best fit your unique design. Each square trim is easy to install and can make an excellent addition to a variety of style settings

7" SQUARE TRIM RING

P860053-009 Brushed Nickel
P860053-020 Antique Bronze
P860053-031 Black
7" sq., 1-1/8" ht.



P860053-009



P860053-020



P860053-031

11" SQUARE TRIM RING

P860054-009 Brushed Nickel
P860054-020 Antique Bronze
P860054-031 Black
11" sq., 1-1/8" ht.



P860054-009



P860054-020



P860054-031

14" SQUARE TRIM RING

P860055-009 Brushed Nickel
P860055-020 Antique Bronze
P860055-031 Black
14" sq., 1-1/8" ht.



P860055-009



P860055-020



P860055-031

Surface Mount Downlighting

Bright, Even Light.

Everlume™ Round Surface Mount LED

Edgelit technology creates a large glare free and evenly illuminated surface for a variety of applications for both residential and commercial applications. Offering a low profile design, LED Everlume™ Round Surface Mount is available in a White finish. The integrated driver does not recess into junction box, allowing for easy installation into 4" octagonal, 4" round PVC and 4-1/2" ceiling pan junction boxes. Wet location listed and offers a 50,000-hour LED life.

5" ROUND
P810024-030-30 White
 5" dia., 1-1/8" ht.
 12w integrated LED
 3000K, 90CRI, 800 lumens.



P810024-030-30

7" ROUND
P810015-030-30 White
 7" dia., 1-1/8" ht.
 15w integrated LED
 3000K, 90CRI, 1000 lumens.



P810015-030-30

11" ROUND
P810016-030-30 White
 11" dia., 1-1/8" ht.
 17w integrated LED
 3000K, 90CRI, 1300 lumens.



P810016-030-30

14" ROUND
P810017-030-30 White
 14" dia., 1-1/8" ht.
 19.5w integrated LED
 3000K, 90CRI, 1700 lumens.



P810017-030-30

18" ROUND
P810018-030-30 White
 18" dia., 1-1/8" ht.
 23w integrated LED
 3000K, 90CRI, 2100 lumens.



P810018-030-30

All fixtures:



LED FEATURES

- Wet location listed.
- Flicker-free dimming with many Triac and ELV dimmers.
- 120v input voltage.
- 50,000 hour life.

Everlume™ Round Trim Accessories

You'll never have to sacrifice function for style with our Everlume™ Round Trim Accessories. This collection offers a variety of finishes and trim ring sizes to best fit your unique design needs. Each trim ring is easy to install in both residential and commercial settings.

5" ROUND TRIM RING
P860048-009 Brushed Nickel
P860048-020 Antique Bronze
P860048-031 Black
 5" dia., 1-1/8" ht.



P860048-009



P860048-020



P860048-031

7" ROUND TRIM RING
P860049-009 Brushed Nickel
P860049-020 Antique Bronze
P860049-031 Black
 7" dia., 1-1/8" ht.



P860049-009



P860049-020



P860049-031

11" ROUND TRIM RING
P860050-009 Brushed Nickel
P860050-020 Antique Bronze
P860050-031 Black
 11" dia., 1-1/8" ht.



P860050-009



P860050-020



P860050-031

14" ROUND TRIM RING
P860051-009 Brushed Nickel
P860051-020 Antique Bronze
P860051-031 Black
 14" dia., 1-1/8" ht.



P860051-009



P860051-020



P860051-031

18" ROUND TRIM RING
P860052-009 Brushed Nickel
P860052-020 Antique Bronze
P860052-031 Black
 18" dia., 1-1/8" ht.



P860052-009



P860052-020



P860052-031

Everlume™ Round Surface Mount LED

Edgelit technology creates a large glare free and evenly illuminated surface for a variety of applications for both residential and commercial applications. Offering a low profile design, LED Everlume™ Round Surface Mount is available in a White finish. The integrated driver does not recess into junction box, allowing for easy installation into 4" octagonal, 4" round PVC and 4-1/2" ceiling pan junction boxes. Wet location listed and offers a 50,000-hour LED life.



LED FEATURES

- Wet location listed.
- Flicker-free dimming with many Triac and ELV dimmers.
- 120v input voltage.
- 50,000 hour life.

5" ROUND

P810024-030-30 White

5" dia., 1-1/8" ht.

12w integrated LED

3000K, 90CRI, 800 lumens.



P810024-030-30

7" ROUND

P810015-030-30 White

7" dia., 1-1/8" ht.

15w integrated LED

3000K, 90CRI, 1000 lumens.



P810015-030-30

11" ROUND

P810016-030-30 White

11" dia., 1-1/8" ht.

17w integrated LED

3000K, 90CRI, 1300 lumens.



P810016-030-30

14" ROUND

P810017-030-30 White

14" dia., 1-1/8" ht.

19.5w integrated LED

3000K, 90CRI, 1700 lumens.



P810017-030-30

18" ROUND

P810018-030-30 White

18" dia., 1-1/8" ht.

23w integrated LED

3000K, 90CRI, 2100 lumens.



P810018-030-30

All fixtures:

