BRYANT®

Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 20′ Length, Red

By Bryant
Catalog # HC5ER20

Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 20′

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC5ER20
Color	Red
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	Mechanical - Cable to plug tensile strength - 20+ lbs.
	Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
	Standard
UPC	662620235912

Dimensions

Length	20 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	ANSI/TIA/EIA-568-C.2 Category 5E Component
	ISO 11801/60603-7-41 Category 5E Component

Product Assets

©2024 Hubbell Incorporated. All rights reserved