BRYANT®

Patch Cord, Speed Gain, Cat5E, Slim, White, 7′

By Bryant
Catalog # HC5EW07

Patch Cord, Speed Gain, Cat 5e, Slim, 7′

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC5EW07
Color	White
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	Mechanical - Cable to plug tensile strength - 20+ lbs.
	Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
	Standard
UPC	662620236513

Dimensions

Length	7 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	ANSI/TIA/EIA-568-C.2 Category 5E Component
	ISO 11801/60603-7-41 Category 5E Component

Product Assets

©2024 Hubbell Incorporated. All rights reserved