BRYANT®

Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1′ Length, Yellow

By Bryant
Catalog # HC5EY01

Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1′ Length, Yellow

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC5EY01
Color	Yellow
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	• Length - 1-Foot • Product - Patch Cords
Temperature Rating	Per TIA
Type	Standard
UPC	662620236711

Dimensions

Length	1 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	Meets And Exceeds ANSI/TIA

Product Assets

Specifications - HC5EY01

©2024 Hubbell Incorporated. All rights reserved