BRYANT®

Patch Cord, Speed Gain, Cat6, Slim, Yellow, 7′

By Bryant
Catalog # HC6Y07

Patch Cord, Speed Gain, Cat 6,Slim, 7′

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6Y07
Color	Yellow
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620233819

Dimensions

Length	7 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	• ANSI/TIA/EIA-568-C.2 Category 6 Component • ISO 11801/60603-7-41 Category 6 Component

Logistics

Carton Quantity	50
Pallet Quantity	2700

Product Assets

Catalog Page - PREM D5 CatalogPage
Catalogs - Premise Wiring Catalog
Specifications - HC6Y07

©2024 Hubbell Incorporated. All rights reserved