BRYANT®

iStation Modules, 3.5 MM Stereo Jack, 2) RCA Audio, 1-Unit, Gray

By Bryant
Catalog # IM35AR1GY

iStation Modules, 3.5 MM Stereo Jack, 2) RCA Audio, 1-Unit, Gray

Features

- 3.5 MM Stereo Jack
- 2) RCA Audio
- 1-Unit
- Gray

Application

2 RCA Left Right Audio W/3.5mm Stereo Audio

General

Catalog Number	IM35AR1GY
Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION Audio/Video Modules
Material - Mounting Hardware	Snap-On- Snap-Fit
Style	L/R Audio, 3.5mm Stereo
Temperature Rating	Per TIA
Type	RCA
UPC	662620214283

Dimensions

Display Size	Standard Sized Product

Electrical Ratings

Connectivity	Plug-N-Play
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Logistics

Carton Quantity	25

Product Assets

Catalog Page - BRY R-18 Catalog Page
Catalogs - Bryant Full Line Catalog
Specifications - IM35AR1GY

©2024 Hubbell Incorporated. All rights reserved