

SPATIAL

Spatial showcases a modern form that complements Urban Industrial, Mid-Century Modern and Bohemian styles. Overscale geometric frames feature designs inspired by metal trusses and the art of engineering. Matte Black finish is highlighted by clear globe shades or open candles. Chandelier and pendant options are ideal for foyers and entryways, while vanity fixtures complement modern spa-like bath suites.



ALSO AVAILABLE IN
Bath



P500083-031



P500082-031




P400077-031



P500083-031



P500096-031



P500084-031



P400084-031

FINISH
● Black - 031

PAIR WITH
Remix
Finn

SEMI-FLUSH CONVERTIBLE
P400077-031 Black
Hanging and ceiling mount hardware included.
19-5/8" dia., 14" ht.
Overall ht. w/chain 52", wire 10'.
Three candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER
P400084-031 Black
26" dia., 32" ht.
Overall ht. w/chain 101", wire 15'.
Six medium base lamps, each 60w max.

MINI-PENDANT
P500082-031 Black
12" dia., 11-1/4" ht.
Overall ht. w/chain 85", wire 10'.
One medium base lamp, 100w max.

FOUR-LIGHT PENDANT
P500083-031 Black
23-1/2" dia., 19" ht.
Overall ht. w/chain 93-1/2", wire 15'.
Four candelabra base lamps, each 60w max.

SIX-LIGHT PENDANT
P500084-031 Black
28" dia., 26" ht.
Overall ht. w/chain 101", wire 15'.
Six candelabra base lamps, each 60w max.

THREE-LIGHT FOYER
P500096-031 Black
23-3/4" dia., 25-1/2" ht.
Overall ht. w/chain 100-1/2", wire 15'.
Three candelabra base lamps, each 60w max.

All fixtures shown with P7826-01 or G16.5 lamps, not included.

SPATIAL

Spatial showcases a modern form that complements Urban Industrial, Mid-Century and Bohemian styles. Overscale geometric frames feature designs inspired by metal trusses and the art of engineering. A Matte Black finish is highlighted by clear globe shades or open candles. Chandelier and pendant options are ideal for foyers and entryways, while vanity fixtures complement modern spa-like bath suites.

ALSO AVAILABLE IN
Collections



P300113-031



P300113-031



P300112-031

FINISH
● Black - 031

ONE-LIGHT BATH
P300112-031 Black
5-3/8" W., 6-1/2" ht.
Extends 8". H/CTR 3-3/8".
One candelabra base lamp,
60w max.

TWO-LIGHT BATH
P300113-031 Black
14-1/8" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Two candelabra base lamps,
each 60w max.

THREE-LIGHT BATH
P300114-031 Black
22" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Three candelabra base lamps,
each 60w max.

FOUR-LIGHT BATH
P300115-031 Black
31-1/8" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Four candelabra base lamps,
each 60w max.

All fixtures mount up or down.



P300114-031



P300115-031