

Derby

FINISH

● Espresso - 84

Derby boasts an Espresso powder coat finish. Features a blown, clear seeded glass diffuser encased in a cast aluminum black frame. Espresso finish on roof and back plate.

P5579-84

Powder Coat Finish *Cast Aluminum*



Clear Seeded Glass

POST LANTERN
P5479-84 Espresso
 8-1/2" dia., 13-3/8" ht.
 Fits 3" post (sold separately).
 One medium base lamp,
 100w max.

HANGING LANTERN
P5579-84 Espresso
 8-1/2" dia., 12-3/8" ht.,
 Overall ht. w/chain 86"; wire 15'.
 One medium base lamp,
 100w max.

SMALL WALL LANTERN
P5749-84 Espresso
 6-1/2" W., 8-3/8" ht.
 Extends 7-5/8". H/CTR 3".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN
P5750-84 Espresso
 8-1/2" W., 11" ht.
 Extends 9-5/8". H/CTR 4-1/4".
 One medium base lamp,
 100w max.

LARGE WALL LANTERN
P5751-84 Espresso
 10-5/8" W., 15" ht.
 Extends 14-1/8". H/CTR 3-3/8".
 One medium base lamp,
 100w max.

FLUSH MOUNT
P6017-84 Espresso
 10" sq., 5-1/2" ht.
 Two medium base lamps,
 each 60w max.



P5749-84



P5579-84



P5750-84



P6017-84



P5751-84



P5479-84

Derby LED

FINISH

● Antique Bronze - 20

Craftsman styling marries traditional and rustic details. Derby boasts an artistic glass diffuser with a die-cast aluminum, powder coated Antique Bronze frame.

P5750-2030K9

Rustic Details



Craftsman Style

Artistic Glass

SMALL WALL LANTERN
P5749-2030K9 Antique Bronze
 6-1/2" W., 8-3/8" ht.
 Extends 7-3/8". H/CTR 3".
 One 9w LED module, 3000K,
 90CRI, 623 source lumens.

LARGE WALL LANTERN
P5751-2030K9 Antique Bronze
 10-5/8" W., 15-1/2" ht.
 Extends 11-5/8". H/CTR 3-3/8".
 One 9w LED module, 3000K,
 90CRI, 623 source lumens.

MEDIUM WALL LANTERN
P5750-2030K9 Antique Bronze
 8-1/2" W., 11-1/4" ht.
 Extends 9-3/8". H/CTR 4-1/4".
 One 9w LED module, 3000K,
 90CRI, 623 source lumens.

All fixtures:



P5749-2030K9



P5750-2030K9



P5751-2030K9