BRYANT®

1-Gang, Plate with 2) Jacks, 6-Position 4-Conductor, Screw Terminals, Light Almond

By Bryant
Catalog # NS742LA



1-Gang, Plate with 2) Jacks, 6-Position 4-Conductor, Screw Terminals, Light Almond

Features

- Meets FCC part 68
- Convenient screw down terminals
- High impact-resistant thermoplastic plate

Application

Communications

General

Catalog Number	NS742LA
Color	Ivory
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	2) 6-Position 4-Conductor Jack
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Size	Standard
Specifications	• Device Type - 6-Position, 4-Conductor • Style - Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Voice
UPC	883778503542

Dimensions

Display Size	Standard Sized Product

Electrical Ratings

Connectivity	Screw Terminals
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	UL Listed

Logistics

Carton Quantity	10

Product Assets

Catalog Page - BRY R-13 Catalog Page
Catalogs - Bryant Full Line Catalog
Specifications - NS742LA

©2024 Hubbell Incorporated. All rights reserved