BRYANT®

Plates, 1-Gang, With F Connector, Light Almond

By Bryant
Catalog # NS750LA

Plates, 1-Gang, With F Connector, Light Almond

Features

- Meets FCC part 68
- Convenient screw down terminals
- High impact-resistant thermoplastic plate

Application

CATV

General

Catalog Number	NS750LA
Color	Light Almond/Office White
Construction	Molded
Construction Material - Main	High-Impact Thermoplastic (UL 94V-0)
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	1) F-Coax Connector
Material	High-Impact Thermoplastic (UL 94V-0)
Material - Mounting Hardware	Screw Mounting
Size	Standard
Specifications	• Device Type - Single F-Type • Style - Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Voice & CATV
UPC	883778504105

Dimensions

Display Size	Standard Sized Product

Electrical Ratings

Connectivity	Female to Female
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	UL Listed

Logistics

Carton Quantity	25
Pallet Quantity	7000

Product Assets

Catalog Page - BRY R-13 Catalog Page
Catalog Page - PREM S14 CatalogPage
Catalogs - Premise Wiring Catalog
Catalogs - Bryant Full Line Catalog
Specifications - NS750LA

©2024 Hubbell Incorporated. All rights reserved