BRYANT®

Plates, 1-Gang, Mid Sized, With F Connector, Jack, 6-Position 6-Conductor, Light Almond

By Bryant
Catalog # NS755LA

Plates, 1-Gang, Mid Sized, With F Connector, Jack, 6-Position 6-Conductor, Light Almond

Features

- Meets FCC part 68
- Convenient screw down terminals
- High impact-resistant thermoplastic plate

Application

Communications/CATV

General

Catalog Number	NS755LA
Color	Light Almond
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	6-Position 6-Conductor Jack, 1) F-Coax Connector
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Size	Midsize
Specifications	• Device Type - 6-Position, 6-Conductor • Style - Mid-Size
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Voice & CATV
UPC	883778504129

Dimensions

Display Size	Standard Sized Product

Electrical Ratings

Connectivity	Female to Female and 110 IDC
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	UL Listed

Logistics

Carton Quantity	10

Product Assets

Catalog Page - BRY R-13 Catalog Page
Catalogs - Bryant Full Line Catalog
Specifications - NS755LA

©2024 Hubbell Incorporated. All rights reserved