BRYANT®

Net Select, Module, Multi Pair, Patchable Cord, Multi Mode

By Bryant
Catalog # NSOMTM24

Net Select, Module, Multi Pair, Patchable Cord, Multi Mode

Features

-
-
-

General

Application	Telephone
Catalog Number	NSOMTM24
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Patchable Telcom Multip
Material - Mounting Hardware	Screw Mounting
Style	Telecom
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Telecom
UPC	883778500411

Dimensions

Display Size	Standard Sized Product

Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	Meets FCC Part 68 Standard
	RoHS Compliant
	UL and cUL Listed

Logistics

Carton Quantity	10

Product Assets

Catalog Page - BRY R-4 Catalog Page
Catalogs - Bryant Full Line Catalog

©2024 Hubbell Incorporated. All rights reserved