


















**Accessories**

Description	Finish	Catalog No.	
<b>Splice Kit</b> (3) piece staked bolt/washer and nut combination; splices straight sections and field formed fittings; 50-pack	Zinc Plated Black Stainless Steel*	<b>HBTSK</b> <b>HBTSKBK</b> <b>HBTSKSS</b>	
<b>Corner Splice</b> (2) 90° splice bars, (8) splice kit sets; Splice fittings required: (1) per tee fitting; (2) per each cross fitting	Zinc Plated Black Stainless Steel*	<b>HBTC</b> <b>HBTCGBK</b> <b>HBTCSS</b>	
<b>Bar Splice</b> Slotted bar 11 <sup>11</sup> / <sub>16</sub> " L; splices straight sections/fittings; bend to form tray reducers; adds rigidity to tray splices; 50-pack	Zinc Plated Black Stainless Steel*	<b>HBTBS</b> <b>HBTBSBK</b> <b>HBTBSS</b>	
<b>Washer Supports</b> Splices straight sections/fittings; also a hold down method for tray to strut (nut and bolt sold separately); 50-pack	Zinc Plated Black Stainless Steel*	<b>HBTWS</b> <b>HBTWSBK</b> <b>HBTWSS</b>	
<b>Self Tapping Screws with Supports</b> 1/4" – 20 self tapping screw and HBTWS; 50-pack	Zinc Plated	<b>HBTUGS</b>	
<b>Vertical Down</b> Protects cables when dropping from the end or side of tray; tray width 7 <sup>3</sup> / <sub>4</sub> " (197); single pack	Zinc Plated Black	<b>HBTVD</b> <b>HBTVDBK</b>	
<b>Radius Down</b> Increases cable protection and cable bend control; single pack	Tray Width: 4" (102) 6" (152) 12" (305)	Black Black Black	<b>HBTRD4BK</b> <b>HBTRD6BK</b> <b>HBTRD12BK</b>
<b>Exit Radius Down*</b> Top tray attachment, increases cable protection and cable bend control; 4X4" minimum tray size; single pack	Black	<b>HBTEXTRDBK</b>	
<b>Cable Drop Outs</b> Install into bottom of basket tray to reduce pinch points and maintain cable radius bend	2" X 4" (51 X 102) 4" X 4" (102 X 102)	Black Black	<b>HBTCDBK</b> <b>HBTC4X4BK</b>
<b>Label Clip</b> Attachment for all tray sizes; single pack	White	<b>HBTL</b>	
<b>Cable Guide*</b> Maintains cable bend radius; acts as divider for straight sections and fittings; single pack	Black	<b>HBTCG</b>	
<b>Electrical Box Bracket</b> Attaches electrical box to side of tray; single pack	Pre-Galvanized Black	<b>HBTEB</b> <b>HBTEBBL</b>	
<b>Sidecar</b> Attaches to outside of tray; provides additional cable support; 2" deep; single pack	Pre-Galvanized Black	<b>HBTSC</b> <b>HBTSCBK</b>	
<b>Strut Clips</b> Used to hold down basket tray when used with any standard industry strut supports; 50-pack	Pre-Galvanized	<b>HBTSTRUTCLIP</b>	
<b>Grounding Split Bolts</b> For supplemental grounding; (1) bolt per section of basket tray; installer must supply 6 AWG grounding wire; 10-pack	Copper Alloy	<b>HBTSPPLITBOLTPK10</b>	
<b>Rack Attachment</b> Attaches tray directly to the top of a standard rack	Zinc Plated Black	<b>HBTRA</b> <b>HBTRABK</b>	
<b>Conduit Attachment</b> Connects conduit to tray (3/4", 1" and 1 1/4" conduit)	Pre-Galvanized Black	<b>HBTC3</b> <b>HBTC3BK</b>	
<b>Nut and Bolt Sets</b> 1/4" – 20 nut and bolt sets; 50-pack	Zinc Plated Stainless Steel*	<b>HBTNB</b> <b>HBTNBSS</b>	
<b>Cutting Tool</b> Manual offset angled cutting tool; 24" leveraged handle; 6lb each		<b>HBTCUTTOOL</b>	

\*Stainless Steel accessories are manufactured from 316 grade