



Thin Wall C-Taps

| Stranded AWG | Stranded AWG | Stranded AWG | Length Inches (mm) | Color Code | No. Ribs | Die Index | HW Series | HU Series | Qty | Catalog No. |
|--------------|--------------|--------------|--------------------|------------|----------|-----------|------------|-----------|-----|------------------|
| 6-6 | | | 1.18" (30) | Brown | 1 | 10 | HW2CVT(2) | HUC4 | 25 | ① HYC4L12 |
| 4-4 | 2-6 | | 1.18" (30) | Pink | 1 | 12 | HW25VT (2) | HUC2 | 25 | HYC2L12 |
| 2-4 | 1-6 | | 1.75" (44) | Black | 2 | 13 | HW26VT (2) | HUC1 | 10 | HYC1L12 |
| 2-2 | 1-4 | 1/0-4 | 1.75" (44) | Orange | 2 | 14 | HW27VT(3) | HU25 | 10 | HYC25L12 |
| 1-1 | 1/0-2 | 2/0-2 | 1.75" (44) | Purple | 2 | 15 | HW28VT(3) | HU26 | 5 | HYC26L12 |
| 1/0-1/0 | 2/0-2 | 3/0-2 | 1.75" (44) | Yellow | 2 | 16 | HW29VT(3) | - | 5 | HYC27L12 |

C-Taps

| Stranded AWG | Stranded AWG | Stranded AWG | Length Inches (mm) | Die Index | HW Series | HU Series | Qty | Catalog No. |
|--------------|--------------|--------------|--------------------|-----------|-----------|-----------|-----|-----------------|
| 6-6 | 4-6 | | 0.625" (16) | BG | HWBG (2) | HUBG (2) | 10 | ② HYC4C6 |
| 4-4 | 4-6 | | 0.625" (16) | BG | HWBG (2) | HUBG (2) | 10 | HYC4C4 |
| 2-4 | 2-6 | | 0.75" (44) | C | HWCC (2) | HUC (2) | 10 | HYC2C4 |
| 2-2 | | | 0.75" (44) | C | HWCC (2) | HUC (2) | 10 | HYC2C2 |
| 2/0-6 | 2/0-4 | 2/0-2 | 0.875" (22) | 0 | - | HU0 | 5 | HYC26C2 |
| 2/0-2/0 | | | 0.875" (22) | 0 | - | HU0 | 5 | HYC26C26 |
| 4/0-6 | 4/0-4 | 4/0-2 | 1.07" (27) | D3 | - | HUD3 | 1 | HYC28C2 |
| 4/0-2/0 | | | 1.07" (27) | D3 | - | HUD3 | 1 | HYC28C26 |
| 4/0-4/0 | | | 1.07" (27) | D3 | - | HUD3 | 1 | HYC28C28 |

H-Taps

| Stranded AWG | Stranded AWG | Stranded AWG | Length Inches (mm) | Color Code | Die Index | HW Series | HU Series | Qty | Catalog No. |
|--------------|--------------|--------------|--------------------|------------|-----------|-----------|-----------|-----|------------------|
| 6-6 | | | 0.6" (15) | Orange | BG | HWBG | HUBG | 1 | ③ HYH6C6C |
| 2-2,4,6 | 4-4,6 | | 0.75" (44) | Brown | C | HWCC | HUC | 1 | HYH2C2C |
| 4/0-2,6 | 2/0-2,6 | 1/0-2,6 | 0.9" (23) | Purple | 654 | - | HU654 | 1 | HYH292C |
| 4/0-4/0,2 | 3/0-3/0,2 | 2/0-2/0,2 | 0.9" (23) | Purple | 654 | - | HU654 | 1 | HYH2929 |
| 500-250,1/0 | 350-250,1/0 | 4/0-1/0 | 1.0" (25) | Brown | 1104 | - | HU1104 | 1 | HYH3429 |
| 500-500,4/0 | 350-350,4/0 | | 1.0" (25) | Brown | 1104 | - | HU1104 | 1 | HYH3434 |
| 750-4/0,1/0 | 650-4/0,1/0 | 500-4/0,1/0 | 0.95 (24) | Yellow | K-R | - | HUKR | 1 | HYH3931 |
| 750-750,350 | 650-650,350 | 500-350 | 1.25 (32) | Yellow | K-R | - | HUKR | 1 | HYH3939 |

H-Taps with Clear Cover

| Stranded AWG | Stranded AWG | Stranded AWG | Length Inches (mm) | Color Code | Die Index | HW Series | HU Series | Qty | Catalog No. |
|--------------|--------------|--------------|--------------------|------------|-----------|-----------|-----------|-----|------------------|
| 6-6 | | | 0.6" (15) | Orange | BG | HWBG | HUBG | 1 | ④ HYH6CWC |
| 2-2,4,6 | 4-4,6 | | 0.75" (44) | Brown | C | HWCC | HUC | 1 | HYH2CWC |
| 4/0-2,6 | 2/0-2,6 | 1/0-2,6 | 0.9" (23) | Purple | 654 | - | HU654 | 1 | HYH29WC |
| 4/0-4/0,2 | 3/0-3/0,2 | 2/0-2/0,2 | 0.9" (23) | Purple | 654 | - | HU654 | 1 | HYH2929WC |

H-Tap Covers

| H-Tap Size | Color Code | Qty | Clear Cover | Black Cover |
|------------|------------|-----|-------------------|----------------|
| HYH6Cxx | Orange | 1 | HCCFBGFR ⑤ | HCFBGFR |
| HYH2Cxx | Brown | 1 | HCCFOFR | HCFOFR |
| HYH29xx | Purple | 1 | HCCDFDR | HCFDFDR |
| HYH34xx | Brown | 1 | HCCFN | HCFN |
| HYH39xx | Yellow | 1 | HCCFR | HCFR |