BRYANT®

Fiber OSP Breakout Kit, 12 Fiber

By Bryant
Catalog # OFBOKT12

Tools, OSP Cable Kit, 900 uM, 12-Fiber.

Features

- 36″ inch length
- 12 colors EIA/TIA-598
- 12 fiber, 900 micron Furcation Assembly
- 2.4mm Jacket Holding Clip
- 3.0mm Jacket Holding Clip
- Ribbon Jacket Holding Clip
- Brass Jacket Crimp
- Fan-out Housing
- Instruction sheet

Application

- OSP Cable Termination

General

Catalog Number	OFBOKT12
EU RoHS Indicator	Yes
Item Type	Tools
Material	PVC (polyvinyl chloride)
Style	OSP Cable Break-Out Kit
Sub Brand	OPTIChannel
Type	Tools
UPC	662620237411

Dimensions

Display Size	900 Micron

Logistics

Carton Quantity	50

Product Assets

Catalog Page - PREM G17 CatalogPage
Catalogs - Premise Wiring Catalog
Literature - FiberHubb™ Splice-On Connectors
Literature - PROclick® Fiber Connectors
Specifications - OFBOKT12

©2024 Hubbell Incorporated. All rights reserved