BRYANT®

# Combination Devices, Residential Grade, Decorator Series, 1) Three Way Pole Rocker, 1) Tamper Resistant Single Receptacle, 15A 120V AC

By Bryant
Catalog # RCD308LATR

Switches and Lighting Controls, Combination Devices, Residential Grade, Decorator Series, 1) Three Way Pole Rocker, 1) Tamper Resistant Single Receptacle, 15A 120V AC, Side

## Application

- Residential

## Performance

- Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute
- Electrical - Endurance - 30,000 cycles minimum
- Electrical - Max. working voltage - 120V
- Electrical - Overload - 1.5 times rating
- Environmental - Flammability - UL V0
- Environmental - Operating temperatures - Maximum continuous 60°C
- minimum -20°C (without impact)
- Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only
- push wire: #14 AWG solid copper wire only

## General

| | |
|---|---|
| Action | Snap Switch |
| Actuator | Rocker |
| Catalog Number | RCD308LATR |
| Contact Configuration | Two Position |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | Decorator Switch and Receptacle Combo Devices |
| Material - Mounting Hardware | Mounting Screws |
| Number Of Poles | 1) Three Way |
| Operating Cycles | 30,000 Minimum |
| Operating Temperature | Max Continuous- 60 Degrees C, Minimum- -20 Without Impact |
| Specifications | • Base and body - PVC<br>• Mounting strap - Galvanized steel<br>• Rocker - Polycarbonate<br>• Terminal screws - Steel<br>• Terminals - Brass |
| UPC | 883778302435 |

## Dimensions

| | |
|---|---|
| Display Size | Standard Size |

## Electrical Ratings

| | |
|---|---|
| Amperage Rating | 15 A |
| Connectivity | Side Wired |
| Contact Rating | 15A |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Voltage Rating | 125 VAC |
| Voltage Rating Description | 125 VAC |
| Wattage | 1875 |

## Certifications And Compliance

| | |
|---|---|
| Industry Standard(s) | • CSA Certified<br>• UL Listed E3896 |

## Logistics

| | |
|---|---|
| Carton Quantity | 10 |

## Product Assets

Catalog Page - WDK Z-4 Catalog Page
Catalogs - WDK Catalog Full 2024
Catalogs - Bryant Full Line Catalog
Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles
Literature - Residential Catalog
Specifications - RCD308LATR

©2024 Hubbell Incorporated. All rights reserved