BRYANT®

Switches and Lighting Controls, Dimmer, Rotary, Single Pole, 600W 120V AC, White

By Bryant
Catalog # RD600RW

Switches and Lighting Controls, Dimmer, Rotary, Single Pole, 600W 120V AC, White

General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Catalog Number	RD600RW
Color	White
Construction	Metal Strap, Polycarbonate Front
EU RoHS Indicator	No
Environmental Conditions	Indoor Use Only
Number Of Poles	Single Pole
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Specifications	• Product Type - Rotary Dimmers • Termination - Single Pole
Style	Rotary Dimmer
Type	Incandescent
UPC	883778117046

Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

Electrical Ratings

Amperage Rating	5 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	600 W

Certifications And Compliance

Industry Standard(s)	UL Listed

Logistics

Carton Quantity	6

Product Assets

Catalog Page - BRY F-15 Catalog Page
Catalogs - Bryant Full Line Catalog
Specifications - RD600RW

©2024 Hubbell Incorporated. All rights reserved