BRYANT®

Switches and Lighting Controls, Dimmer Switch, Illuminated Rocker, Single Pole, 1000 Watts 1200V AC, Light Almond

By Bryant
Catalog # RDV10PLA

Switches and Lighting Controls, Dimmer Switch, Illuminated Rocker, Single Pole, 1000 Watts 1200V AC, Light Almond

General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Catalog Number	RDV10PLA
Color	Light Almond
Construction	Metal Strap, Polycarbonate Front
EU RoHS Indicator	No
Environmental Conditions	Indoor Use Only
Number Of Poles	Single Pole
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Specifications	• Product Type - Rocker Decorator Dimmers • Termination - Single Pole
Style	Rocker Dimmer
Type	Incandescent
UPC	883778116124

Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

Electrical Ratings

Amperage Rating	8 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	1000 W

Certifications And Compliance

Industry Standard(s)	CSA Certified

Logistics

Carton Quantity	6

Product Assets

Specifications - RDV10PLA

©2024 Hubbell Incorporated. All rights reserved