

Pin and Sleeve Devices/Mechanical Interlocks

Accessories

Closure Caps

Cap assemblies provide watertight sealing to a disconnected male IEC Pin and Sleeve plug or inlet. Manufactured of the same tough non-metallic material as the watertight IEC Pin and Sleeve devices for corrosion and abuse resistance.

| Description | Catalog Number |
|---|----------------|
| Fits all 16 and 20A, 3 wire plugs and inlets. | PC320 |
| Fits all 16 and 20A, 4 wire plugs and inlets. | PC420 |
| Fits all 16 and 20A, 5 wire plugs and inlets. | PC520 |
| Fits all 30 and 32A, 3 and 4 wire plugs and inlets. | PC3430 |
| Fits all 30 and 32A, 5 wire plugs and inlets. | PC530 |
| Fits all 60 and 63A plugs and inlets. | PC60 |
| Fits all 100 and 125A plugs and inlets. | PC100 |



PC3430

Cover Assemblies

Replacement cover assemblies for use with watertight connector bodies and receptacles. Exact replacement cover assemblies required to maintain proper water ingress. They are not reverse compatible. Replacement covers are not interchangeable. Kit contains cover, arm assembly and installation tool.

| Description | IP67 Catalog Number | IP69k/4X Catalog Number |
|--|---------------------|-------------------------|
| Fits all 16 and 20A, 3 wire watertight female devices. | CA320 | HBLCA320 |
| Fits all 16 and 20A, 4 wire watertight female devices. | CA420 | HBLCA420 |
| Fits all 16 and 20A, 5 wire watertight female devices. | CA520 | HBLCA520 |
| Fits all 30 and 32A, 3 and 4 wire watertight female devices. | CA3430 | HBLCA3430 |
| Fits all 30 and 32A, 5 wire watertight female devices. | CA530 | HBLCA530 |
| Fits all 60 and 63A watertight female devices. | CA60 | HBLCA60 |
| Fits all 100 and 125A watertight female devices. | CA100 | HBLCA100 |



CA60



HBLCA60

Cord Clamp and Locking Ring

Replacement cord clamp and locking ring for use with IEC plugs, connectors and inlets.

| Description | Cord Clamp and Locking Ring | Locking Ring Only |
|---|-----------------------------|-------------------|
| Fits all 16 and 20A, 3 wire plugs, connectors and inlets. | CC320 | LR320* |
| Fits all 16 and 20A, 4 wire plugs, connectors and inlets. | CC420 | LR420* |
| Fits all 16 and 20A, 5 wire plugs, connectors and inlets. | CC520† | LR520* |
| Fits all 30 and 32A, 3 and 4 wire plugs, connectors and inlets. | CC3430 | LR3430* |
| Fits all 30 and 32A, 5 wire plugs, connectors and inlets. | CC530† | LR530* |
| Fits all 60 and 63A plugs, connectors and inlets. | CC60 | LR60* |
| Fits all 100 and 125A plugs, connectors and inlets. | CC100 | LR100* |

Note: *Locking Ring only for plugs and inlets.

†Consult factory.



CC3430



LR3430

Liquidtight Adapters

Machined aluminum or non-metallic adapters are available to provide a means for attaching flexible liquidtight metal conduit to rear of a Hubbell Pin and Sleeve plug or connector. To install, remove cord grip and two gland cap screws. Use screws to attach adapter. Kellems® liquidtight conduit connectors are available to control arc of bend and to prevent conduit pull-out where vibration, motion or strain is present. These grips interface directly with Hubbell's liquidtight adapters and are available in a wide variety of NPT sizes and configurations. Consult your local code grounding requirements before using liquidtight adapters.

| Rating of Hubbell Pin and Sleeve Device | Liquidtight Conduit Size | Liquidtight Adapters | | Optional Kellems Liquidtight Conduit Grip |
|---|--------------------------|----------------------|-----------------|---|
| | | Aluminum | Non-Metallic | |
| 16 and 20 Amp 3 and 4 Wire | ½" NPT | SAA12 | — | 074093402 |
| | ¾" NPT | SAA34 | — | 074093403 |
| 16 and 20 Amp 5 wire and 30 and 32 Amp 3 and 4 wire | ½" NPT | SAB12 | — | 074093402 |
| | ¾" NPT | SAB34 | — | 074093403 |
| | 1" NPT | SAB100 | — | 074093404 |
| 30 and 32 Amp 5 wire and 60 and 63 Amp (all) | ½" NPT | SAC12 | SAC12NM | 074093402 |
| | ¾" NPT | SAC34 | SAC34NM | 074093403 |
| | 1" NPT | SAC100 | SAC100NM | 074093404 |
| | 1¼" NPT | SAC125 | — | 074093405 |
| 100 and 125 Amp (all) | 1¼" NPT | SAD125 | — | 074093405 |
| | 1½" NPT | SAD150 | — | 074093406 |



SAB34



074093403