BRYANT®

Lamp Holders and Sockets, Medium Base, Pre-Focus, 1000W 250V, Porcelain

By Bryant
Catalog # RL3742

Lamp Holders and Sockets, Medium Base, Pre-Focus, 1000W 250V, Porcelain

Features

- Medium Base
- Pre-Focus
- 1000W 250V
- Porcelain

Application

HID Incandescent

Performance

- Electrical - Rating - 1500W, 600V Max, 5KV Pulse
- Mechanical - Terminal Accommodation - Wire leads: #14 AWG SF-2 (SEW-2) 200° C, 600V glass braid, 12 inch long, stripped 1/2 inch wire

General

Catalog Number	RL3742
Color	White
EU RoHS Indicator	Yes
Item Type	Replacement Incandescent Lampholders
Lamp Size	Mogul Base
Material	Composite
Material - Mounting Hardware	Screw Mounting
Series	Lampholders
Specifications	• Lamp Type - Bayonet socket • Material - Glazed porcelain body with ceramic arc shield Screw shell: Brass with nickel plate • Mounting - Screw mount
Type	HID Incandescent, Porcelain Keyless
UPC	883778118166

Electrical Ratings

Amperage Rating	4.8 A
Connectivity	Screw Terminals
Current / Amperage Rating	4.8 A
Current Rating	4.8 A
Frequency Rating	60 Hz
Voltage Rating	250V AC kV

Certifications And Compliance

Industry Standard(s)	C/US UL Listed

Logistics

Carton Quantity	50
Pallet Quantity	4900

Product Assets

Catalog Page - WDK BB-8 Catalog Page
Catalogs - WDK Catalog Full 2024
Catalogs - Bryant Full Line Catalog
Specifications - RL3742

©2024 Hubbell Incorporated. All rights reserved