BRYANT®

TradeSelect, Straight Blade Devices, Receptacles, Residential Grade, Tamper Resistant Clock Hanger, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White

By Bryant
Catalog # RR151CHWTR

TradeSelect, Straight Blade Devices, Receptacles, Residential Grade, Tamper Resistant Clock Hanger, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White

Features

- Residential Grade
- Tamper Resistant Clock Hanger

Application

Special Use Products

General

Catalog Number	RR151CHWTR
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Special Use
Style	Clock Hanger / Recessed Receptacles
Type	Single Receptacle
UPC	883778302183

Dimensions

Display Size	Standard Sized Product

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	2800

Product Assets

Catalog Page - WDK Z-18 Catalog Page
Catalogs - WDK Catalog Full 2024
Catalogs - Bryant Full Line Catalog
Literature - Home Entertainment
Literature - Residential Catalog
Specifications - RR151CHWTR

©2024 Hubbell Incorporated. All rights reserved