BRYANT®

TradeSelect, Straight Blade, Single Panel Mount Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30R, Black

By Bryant
Catalog # RR430PM

TradeSelect, Straight Blade, Single Panel Mount Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30R, Black

Features

- Single Panel Mount Receptacle
- 30A 125/250V
- 3-Pole 4-Wire Grounding

Application

Residential Range and Dryer Devices

General

Catalog Number	RR430PM
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Heavy Duty
Type	Single Receptacle
UPC	883778100727

Dimensions

Display Size	Standard Sized Product

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	7500

Conductor Related

Number Of Wires	4-Wire
Wire Size	#10 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	14-30R

Logistics

Carton Quantity	50

Product Assets

Catalog Page - WDK Z-17 Catalog Page
Catalogs - WDK Catalog Full 2024
Catalogs - Bryant Full Line Catalog
Specifications - RR430PM

©2024 Hubbell Incorporated. All rights reserved