BRYANT®

TradeSelect, Switches and Lighting Control, Residential Grade, Motor Speed Control, Slider Type, Single Pole, 1.5A 120V AC, White

By Bryant
Catalog # RSFSQFW

tradeSELECT® Residential Grade, Motor Speed Control, Slider Type, Single-Pole, 1.5A 120V AC

General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Catalog Number	RSFSQFW
Color	White
Construction	Metal Strap, Polycarbonate Front
EU RoHS Indicator	No
Environmental Conditions	Indoor Use Only
Number Of Poles	Single Pole
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Specifications	• Product Type - Fan Speed Controls • Termination - Single Pole
Style	Slider Fan Control
Type	Fan Control
UPC	883778116520

Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

Electrical Ratings

Amperage Rating	1.5 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	180 W

Certifications And Compliance

Industry Standard(s)	CSA Certified

Logistics

Carton Quantity	24

Product Assets

Catalog Page - WDK Z-19 Catalog Page
Catalogs - WDK Catalog Full 2024
Catalogs - Bryant Full Line Catalog
Specifications - RSFSQFW

©2024 Hubbell Incorporated. All rights reserved