

SystemOne Recessed 8 Inch FRPT and Covers, for Use In Concrete Floors



S1R8PTFIT1



S1R8PTFIT13



S1R8PTFIT2CHI



S1R8JNC1



S1R8JNC3



S1R8JNC6



S1R8JNC10



S1R8PPT



S1R8ADMTBK



S1R8DIV



S1FRPTJB

8 Inch Fire-Rated Poke-Throughs

Description	Catalog Number
8 Inch Fire-Rated Poke-Through includes: (1) ¼ inch power EMT plus (1) S1FRPTJB box and flexible metal conduit. S1R8JNCxx Series fitting box not included.	S1R8PTFIT
8 Inch Fire-Rated Poke-Through includes: (1) ¼ inch power EMT plus (1) S1R8JNC1 with (1) 1 inch EMT and (1) 1½ inch EMT. (1) S1FRPTJB box and flexible metal conduit.	S1R8PTFIT1
8 Inch Fire-Rated Poke-Through includes: (1) ¼ inch power EMT plus (1) S1R8JNC2 with (2) 1 inch EMT (1) S1FRPTJB box and flexible metal conduit.	S1R8PTFIT2
8 Inch Fire-Rated Poke-Through includes: (1) ¼ inch power EMT plus (1) S1R8JNC3 with (1) 2 inch EMT (1) S1FRPTJB box and flexible metal conduit.	S1R8PTFIT3
8 Inch Furniture Feed Fire-Rated Poke-Through includes: S1R8PTFFCOMPKIT (see below). S1FRPTJB box or flexible metal conduit not included. Approved for use in the City of Chicago.	S1R8PTFIT13
8 Inch Fire-Rated Poke-Through includes: (1) ¼ inch power EMT plus (1) S1R8JNC1 with (1) 1 inch EMT and (1) 1½ inch EMT. S1FRPTJB box or flexible metal conduit not included.	S1R8PTFIT1CHI
8 Inch Fire-Rated Poke-Through includes: (1) ¼ inch power EMT plus (1) S1R8JNC2 with (2) 1 inch EMT. S1FRPTJB box or flexible metal conduit not included.	S1R8PTFIT2CHI
8 Inch Fire-Rated Poke-Through includes: (1) ¼ inch power EMT plus (1) S1R8JNC3 with (1) 2 inch EMT. S1FRPTJB box or flexible metal conduit not included.	S1R8PTFIT3CHI

Note: See page P-37 for technical information.

Recessed 8 Inch Covers

8 Inch FRPT cover assembly unit includes solid cast aluminum construction, carpet gasket and mounting hardware. All covers are UL514A, scrubwater compliant. Furniture Feed covers includes (1) 2" Threaded Hub & (1) 1" Threaded Hub with 3/4" Reducer.



Finish	Catalog Number	Furniture Feed Option
Brushed Aluminum	S1R8CVRALU	S1R8FFCVRALU
Black Powder Coat	S1R8CVRBLK	S1R8FFCVRBLK
Brushed Brass Plated	S1R8CVRBRS	S1R8FFCVRBRS
Antique Bronze Plated	S1R8CVRBRZ	S1R8FFCVRBRZ
Gray Powder Coat	S1R8CVRGRY	S1R8FFCVRGRY
Satin Nickel Plated	S1R8CVRNKL	S1R8FFCVRNKL

Note: COVER LOAD RATING: 1,000 lbs with 2x safety factor. Load applied through a 3" (76mm) dia. mandrel at the center of the cover. Rated for static loads only.

Fitting Boxes

Description	Catalog Number	Description	Catalog Number
(1) 1½ inch & (1) 1 inch EMT.	S1R8JNC1	(1) ¼ inch & (1) 1¼ inch EMT.	S1R8JNC8
(2) 1 inch EMTs.	S1R8JNC2	(1) ¼ inch & (2) 1¼ inch EMTs.	S1R8JNC9
(1) 2 inch EMT.	S1R8JNC3	(1) 1¼ inch & (1) 2 inch EMT.	S1R8JNC10
(3) 1 inch EMTs.	S1R8JNC4	(1) 1½ inch & (1) 2 inch EMT.	S1R8JNC11
(1) 1½ inch & (1) 1¼ inch EMT.	S1R8JNC5	(3) 1¼ inch EMTs.	S1R8JNC12
(2) 1¼ inch EMTs.	S1R8JNC6	(1) 1 inch & (1) 2 inch EMTs.	S1R8JNC13
(1) ¼ inch & (2) 1 inch EMTs.	S1R8JNC7		

8 Inch Accessories

Description	Catalog Number	Description	Catalog Number
Includes components to convert installed 8" Recessed FRPT to Furniture Feed activation; S1R8JNC13, low voltage dividers, internal and external intumescent materials.	S1R8PTFFCOMPKIT	1 Inch replacement Plug, Brushed Aluminum	S1RPLUG100ALU
		1 Inch replacement Plug, Black Powder	S1RPLUG100BLK
		1 Inch replacement Plug, Brass Plated	S1RPLUG100BRS
		1 Inch replacement Plug, Bronze Plated	S1RPLUG100BRZ
		1 Inch replacement Plug, Gray Powder	S1RPLUG100GRY
Pre-pour tube, includes hardware.	S1R8PPT*	1 Inch replacement Plug, Nickel Plated	S1RPLUG100NKL
Abandonment plate, black finish.	S1R8ADMTBK	Power junction box	S1FRPTJB
Low voltage replacement divider.	S1R8DIV		

Note: *Not UL Listed.