


## Traditional Flush Duplex FRPT 3 Inch Core Hole Units, for Use In Concrete Floors

### Flush Duplex FRPT, One-Piece Units

Description	Color	Catalog Number	Description	Color/Material	Catalog Number
Flush Poke-Through	Black Brown Gray Ivory Gray Ivory	<b>PT7FSDBLA</b> <b>PT7FSDBRA</b> <b>PT7FSDGYA</b> <b>PT7FSDIA</b> <b>PT7IGFSDGYA*</b> <b>PT7IGFSDIA*</b>	Flush Brass Poke-Through	All Brass Black/Brass All Brass	<b>PT7FSDBRS2A</b> <b>PT7FSDBRS3A</b> <b>PT7IGFSDBRSA*</b>

Complete assembled unit includes:

- Pre-wired 20A duplex receptacle
- Non-metallic flip lid cover with (2) ½ in. diameter low voltage feed-through holes
- Painted aluminum flange



Complete assembled unit includes:


- Pre-wired 20A duplex receptacle
- All brass or black non-metallic cover option
- Flip lid cover with (2) ½ in. diameter low voltage feed-through holes
- Solid brass flange



Note: \*Includes pre-wired 20A isolated ground duplex receptacle.

### Flush FRPT, Two-Piece Units

Description	Catalog Number
Multi-Channel Through-Floor Fitting with (1) ¼ in. EMT stem for power and (2) ½ in. low voltage feed-through holes.	<b>PT7FSD</b> (with Junction Box) <b>PT73SD</b> (without Junction Box)



Specifications:


- 1 – 4 hour fire rating (1 – 3 hour for steel floor units and concrete topping, D900 Series Design)
- For 2¼ in. to 7 in. floor thickness
- UL installation spacing – minimum 2 ft. on center and not more than one per 65 sq. ft. of floor area

### Service Fittings

Description	Color	Catalog Number	Description	Color/Material	Catalog Number
Flush Aluminum Service Fitting	Black Brown Gray Ivory	<b>FRFBLA</b> <b>FRFBRA</b> <b>FRFGYA</b> <b>FRFIA</b>	Flush Brass Service Fitting	Solid Brass	<b>FRFBRS2A</b>


Complete assembled unit includes:

- Pre-wired 20A duplex receptacle
- Non-metallic flip lid cover with (2) ½ in. diameter low voltage feed-through holes
- Painted aluminum flange



Complete assembled unit includes:

- Pre-wired 20A duplex receptacle
- Solid brass flip lid cover with (2) ½ in. diameter low voltage feed-through holes
- Solid brass flange



### Accessories

Description	Color	Catalog Number	Description	Color/Material	Catalog Number
Non-metallic Replacement Covers	Black Brown Gray Ivory	<b>PFBRCBLA</b> <b>PFBRCBRA</b> <b>PFBRCGYA</b> <b>PFBRCIA</b>	All Brass Replacement Covers	Solid Brass	<b>BRS2RCA</b>





Note: See page P-35 for 3 Inch FRPT accessories.  
See page P-43 for technical information.