

HBL4750 Series

HBL4750 Series	Description	Color	Catalog Number	Description	Color	Catalog Number
	Single Channel Base Packed 50 ft. (15.24m) per carton, 10 ft. (3m) lengths. Assembled cover and base dimensions. W: 4.75" (120.65) H: 1.75" (44.45)	Ivory	HBL4750B10IV	5 Ft. Cover Packed 50 ft. (15.24m) per carton, 5 ft. (1.5m) lengths. 31 In. Precut Cover* For 36 in. (915.00) centers with HBL4747 and HBL4750 Plates. 19 In. Precut Cover* For 24 in. (610.00) centers with HBL4747 and HBL4750 Plates. 13 In. Precut Cover* For 18 in. (457.00) centers with HBL4747 and HBL4750 Plates. 7 In. Precut Cover* For 12 in. (305.00) centers with HBL4747 and HBL4750 Plates.	Ivory	HBL4750CIV
		Gray	HBL4750B10GY		Gray	HBL4750CGY
		A: 120.00" (3048.00) B: 4.75" (120.65) C: 1.62" (41.20)			Ivory	HBL4750C315IV
					Gray	HBL4750C315GY
					Ivory	HBL4750C195IV
		Gray	HBL4750C195GY			
		Ivory	HBL4750C135IV			
		Gray	HBL4750C135GY			
		Ivory	HBL4750C075IV			
		Gray	HBL4750C075GY			

Note: *Packed 10 pieces per carton. Device centers vary based on cover selection. Consult factory for details.

Fittings	Description	Color	Catalog Number	Description	Color	Catalog Number	
	Divider Divides HBL4750 Raceway into two channels. Packed 50 ft. (15.24m) per carton, 5 ft. (1.5m) lengths. HBL4751DA Divider Clips are required to hold divider in place.	Painted Steel	HBL4750DGY	A: 60.00" (1,524.0) B: 1.51" (38.46)	By-Pass Divider Divides HBL4750 Raceway into two channels with a 70/30 split. Allows for a larger power or datacom wire fill. HBL4751DA Divider Clips are required to hold divider in place.	Painted Steel	HBL4750BP
	Divider Clip Required for holding HBL4750DGY in place. Use one every 2.5 ft. (.762m).	Steel**	HBL4751DA	Wire Clip (Plated) For holding conductors in place.	Steel**	HBL4750WCGY	
			A: 4.64" (117.77) B: 1.46" (37.07)			A: 4.60" (116.74) B: 1.58" (40.13) C: 1.00" (25.40)	
	Internal Corner Coupling (Plated) Concealed fitting for making an internal corner while continuing original run in a straight line.	Steel**	HBL4717TCAGY	Coupling (Plated) For joining lengths of HBL4750 Raceway. Sold in pairs.	Steel**	HBL4751AC	
			A: 4.59" (116.59) B: 2.71" (68.73) C: 1.47" (37.34)			A: 1.47" (37.30) B: .42" (10.59)	

Note: **Galvanized Steel.

Dimensions in Inches (mm)