

## Plates, Frames and Modular Connector Fittings

<b>1-Gang and 2-Gang "KP" Plates</b>	Color	Catalog Number	Catalog Number	Catalog Number	Catalog Number	Catalog Number
	Black	<b>KP8BK</b>	<b>KP26BK</b>	<b>KP1BK</b>	<b>KP7BK</b>	<b>KP720BK</b>
	White	<b>KP8W</b>	<b>KP26W</b>	<b>KP1W</b>	<b>KP7W</b>	<b>KP720W</b>
	Off. White	<b>KP8</b> Duplex	<b>KP26</b> Style Line®	<b>KP1</b> Toggle	<b>KP7</b> Recept. (1.41 ID)	<b>KP720</b> Recept. (1.60 ID)
	Black	<b>KP14BK</b>	<b>KP212BK</b>	<b>KP2140BK</b>	<b>KP2162BK</b>	<b>KP2163BK</b>
White	<b>KP14W</b>	<b>KP212W</b>	<b>KP2140W</b>	<b>KP2162W</b>	<b>KP2163W</b>	
Off. White	<b>KP14</b> Blank	<b>KP212</b> Coax (2)	<b>KP2140</b> Jack/Coax	<b>KP2162</b> Modular Jacks (2)	<b>KP2163</b> Modular Jacks (3)	
Black	<b>KPORTBK</b>	<b>KPPANBK</b>	<b>KPIMBZBK</b>			
White	<b>KPORTW</b>	<b>KPPANW</b>	<b>KPIMBZW</b>			
Off. White	<b>KPORTOW</b> Ortronics Series II® Data Module	<b>KPPANOW</b> Panduit Mini-Com® Data Module	<b>KPIMBZOW</b> 3-Unit iSTATION (Accepts all Hubbell iSTATION Modules located in Network Wiring section Y)			
Black	<b>KP82BK</b>	<b>KP262BK</b>	<b>KP2BK</b>	<b>KP24BK</b>		
White	<b>KP82W</b>	<b>KP262W</b>	<b>KP2W</b>	<b>KP24W</b>		
Off. White	<b>KP82</b> 2-Gang Duplex	<b>KP262</b> 2-Gang Style Line®	<b>KP2</b> 2-Gang Toggle	<b>KP24</b> 2-Gang Blank		

Note: 2-Gang "KP" plates, for use with PT12TGB and PW1TGB only.

<b>Comm. "IFP" Plates &amp; Frames</b>	Color	Catalog Number	Catalog Number	Catalog Number	Catalog Number	Catalog Number
	Office	<b>IFP126OW</b>	<b>ISF2OW</b>	<b>ISF3OW</b>	<b>ISF4OW</b>	<b>ISF6OW</b>
	White	Style Line®	Style Line® 2-Port	Style Line® 3-Port	Style Line® 4-Port	Style Line® 6-Port
	Office	<b>IFP18OW</b>	<b>BR106C</b>	<b>Q1060</b>	<b>IFP12OW</b>	<b>IFP13OW</b>
	White	Duplex	Duplex 2-Port	Duplex 4-Port	Flush 2-Port	Flush 3-Port
	Office	<b>IFP14OW</b>	<b>IFP16OW</b>	<b>IFP26OW</b>	<b>IFP29OW</b>	<b>IFP212OW</b>
	White	Flush 4-Port	Flush 6-Port	2-Gang 6-Port	2-Gang 9-Port	2-Gang 12-Port

<b>Frames &amp; Modules</b>	Description	Color	1-Gang	2-Gang
	Front loading plate will accept any modules in three unit combinations. Angled fixtures to be used in bottom opening only. See section Y for additional information on Hubbell iSTATION modules. Each gang accepts 3 module units.	Office White	<b>IMF1OW</b>	<b>IMF2OW</b>

Modular connectors to be used with any plate with a standard modular opening. Not recommended for use with KP plates. For KP applications use KPIMBZOW bezel and appropriate Hubbell iSTATION modules located in section Y. See section Y for additional information on modular connectors.

<b>Modular Connector Fittings</b>	Color	Catalog Number	Catalog Number	Catalog Number
	Office White	<b>SFFX</b> F-Connector	<b>SFSTSOW</b> ST Fiber Connector	<b>SFB10</b> Blank (10 Pack)
	Black housing only	<b>SFRC110R</b> RCA 110 Punchdown	<b>SFSV110BK</b> Super S-Video	<b>FASTSCDSC6</b> SC to ST Duplex Adapter

<b>Xcelerator Modular Jacks</b>	Color	Catalog Number	Catalog Number	Catalog Number
	Office White	<b>HXJ5EOW</b> Cat. 5e, T568A, T568B, RJ45	<b>HXJ6OW</b> Cat. 6, T568A, T568B, RJ45	<b>HXJUOW</b> 6 Position USOC, RJ25

Note: See section Y for additional Hubbell Xcelerator modular jacks and colors.

Panduit® and Mini-Com® are registered trademarks of Panduit Corp.  
Ortronics® and Series II® are registered trademarks of Ortronics/Legrand.