

Straight Blade Devices

15 and 20 Ampere, 125 Volts

IP20
SUITABILITY



15A 125V
NEMA 5-15R
UL CSA
0.5 HP



20A 125V
NEMA 5-20R
UL CSA
1 HP

EdgeConnect™ HBL® Extra Heavy Duty Max Hospital Grade Receptacles

Duplex	Color	Catalog Number	
Hospital Grade, Finder Groove Face, Spring Termination	Black	HBL8200STBK	HBL8300STBK
	Blue	HBL8200STBL	HBL8300STBL
	Brown	HBL8200ST	HBL8300ST
	Gray	HBL8200STGY	HBL8300STGY
	Green	HBL8200STGN	HBL8300STGN
	Ivory	HBL8200STI	HBL8300STI
	Light Almond	HBL8200STLA	HBL8300STLA
	Orange	HBL8200STO	HBL8300STO
	Red	HBL8200STR	HBL8300STR
	White	HBL8200STW	HBL8300STW



HBL8200STBK



HBL2182STGY



HBL2172STOTR



HBL2182STRTR



HBL5362STBK

EdgeConnect™ Style Line® Decorator*

Hospital Grade, Decorator, Spring Termination	Black	HBL2172STBK	HBL2182STBK
	Blue	HBL2172STBL	HBL2182STBL
	Brown	HBL2172ST	HBL2182ST
	Gray	HBL2172STGY	HBL2182STGY
	Green	HBL2172STGN	HBL2182STGN
	Ivory	HBL2172STI	HBL2182STI
	Light Almond	HBL2172STLA	HBL2182STLA
	Orange	HBL2172STO	HBL2182STO
	Red	HBL2172STR	HBL2182STR
	White	HBL2172STW	HBL2182STW
	Hospital Grade, Tamper-Resistant, Decorator, Spring Termination	Black	HBL2172STBKTR
Blue		HBL2172STBLTR	HBL2182STBLTR
Brown		HBL2172STTR	HBL2182STTR
Gray		HBL2172STGYTR	HBL2182STGYTR
Green		HBL2172STGNTR	HBL2182STGNTR
Ivory		HBL2172STITR	HBL2182STITR
Light Almond		HBL2172STLATR	HBL2182STLATR
Orange		HBL2172STOTR	HBL2182STOTR
Red		HBL2172STRTR	HBL2182STRTR
White		HBL2172STWTR	HBL2182STWTR

EdgeConnect™ HBL® Extra Heavy Duty Max Specification Grade Receptacles

Duplex	Color	Catalog Number	
Finder Groove Face, Spring Termination	Black	HBL5262STBK	HBL5362STBK
	Blue	HBL5262STBL	HBL5362STBL
	Brown	HBL5262ST	HBL5362ST
	Gray	HBL5262STGY	HBL5362STGY
	Green	HBL5262STGN	HBL5362STGN
	Ivory	HBL5262STI	HBL5362STI
	Light Almond	HBL5262STLA	HBL5362STLA
	Orange	HBL5262STO	HBL5362STO
	Red	HBL5262STR	HBL5362STR
	White	HBL5262STW	HBL5362STW
	Tamper-Resistant, Smooth Face, Spring Termination	Black	HBL5262STBKTR
Blue		HBL5262STBLTR	HBL5362STBLTR
Brown		HBL5262STTR	HBL5362STTR
Gray		HBL5262STGYTR	HBL5362STGYTR
Green		HBL5262STGNTR	HBL5362STGNTR
Ivory		HBL5262STITR	HBL5362STITR
Light Almond		HBL5262STLATR	HBL5362STLATR
Orange		HBL5262STOTR	HBL5362STOTR
Red		HBL5262STRTR	HBL5362STRTR
White		HBL5262STWTR	HBL5362STWTR

Dimensions in Inches (mm)