BRYANT®

Wallplates and Boxes, Metallic Plates, 2- Gang, 1) 2.66″ Opening, Standard Size, Stainless Steel

By Bryant
Catalog # SS716



Wallplates and Boxes, Metallic Plates, 2- Gang, 1) 2.66″ Opening, Standard Size, Stainless Steel

Features

- Ideal for highly corrosive environments
- Non-magnetic
- Protective plastic film helps to prevent scratches and damage

Application

Protection against contact of live terminals and wiring. Provides finished look to installation.

General

Catalog Number	SS716
Construction	Stamped
Cutout	1) 2.66″ Opening
EU RoHS Indicator	Yes
Item Type	Screw Mount
Material	Stainless Steel, Type 302/304
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	2-Gang
Orientation	Vertical Mount
Size	Standard
Specifications	• Appearance - Horizontal brushed appearance • Mounting Screws - 302/304 SS, Slotted head • Plate Material - Stainless steel 302/304 • Plate Openings - Single Receptacle • Plate Type - 2-Gang • Thickness - Stainless steel 302/304
Style	1-Single - 2.66 in. Hole
Type	Single
UPC	883778201141

Dimensions

Display Size	Standard Sized
Thickness	0.035

Certifications And Compliance

Industry Standard(s)	UL Listed

Logistics

Carton Quantity	10

Product Assets

Catalog Page - WDK N-8 Catalog Page
Catalogs - WDK Catalog Full 2024

©2024 Hubbell Incorporated. All rights reserved