BRYANT®

# Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 2.50-2.99″ Cable Range

By Bryant
Catalog # SSR250

Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 2.50-2.99″ Cable Range

## Application

General Cable Pulling

## General

| | |
|---|---|
| Approx Breaking Strength | 11,000 lbs |
| Catalog Number | SSR250 |
| Construction | Woven |
| EU RoHS Indicator | Yes |
| Load Capacity | 2200 |
| Material | Steel, Galvanized |
| Material - Mounting Hardware | Non-Mounted |
| OEM Brand Name | Hubbell Bryant |
| Series | Slack Grip |
| Style | Split Mesh, Rod Closing, Single Weave |
| Type | Offset Eye |
| UPC | 781786271845 |

## Conductor Related

| | |
|---|---|
| Cable Diameter Range | 2.50 in-2.99 in |
| Cable Size | 2.50-2.99″ (6.35-7.59) |
| Cable Specification | UL Listed Circuit Wire |

## Product Assets

Catalog Page - BRY N-7 Catalog Page
Catalogs - Bryant Full Line Catalog
Specifications - SSR250



©2024 Hubbell Incorporated. All rights reserved