# Vertical Pin Standoff Bracket,18″ w/ Nylon

By Chance
Catalog # 1SBH18V2

Bracket, 18″ Heavy Duty Single-Phase Vertical Pin Standoff

*Representative Image

## Features

- Vertical Position Pin Type Insulator Bracket
- 2″ (heavy duty) fiberglass rod
- 15° Angle
- Base and end fittings are hot dip galvanized ductile iron

## General

| | |
|---|---|
| Catalog Number | 1SBH18V2 |
| Description - End Fitting | Vertical Pin |
| Material - Threads | Nylon |
| Strength Rating - Minimum Ultimate, Longitudinal (L) | 1950 lb |
| Strength Rating - Minimum Ultimate, Transverse (T) | 2500 lb |
| Strength Rating - Minimum Ultimate, Vertical (V) | 2250 lb |
| UPC | 096359565611 |

## Dimensions

| | |
|---|---|
| Diameter - Rod / Tube | 2 in |
| Dimensions | 18 in x 18 in x 4.25 in |
| Distance From Pole | 18 in |
| Height | 4.25 in |
| Length | 18 in |
| Mounting Bolt Spacing | • 8 in<br>• 10 in |
| Weight | 14.9 lb |
| Width | 18 in |

## Electrical Ratings

| | |
|---|---|
| Phase | 1-Phase |

## Logistics

| | |
|---|---|
| Standard Package | 1 |

## Product Assets

Catalog Page - CHANCE® Fiberglass Construction Products
Catalogs - CHANCE® Fiberglass Construction Products
Literature - Nylon Pin Bracket
Sales Drawings - 2″ Vertical Pin Standoff Bracket
Specifications - 1SBH18V2



©2024 Hubbell Incorporated. All rights reserved