Horizontal Pin Standoff Bracket, 24″

By Chance
Catalog # 1SBH24H2

24″ Heavy Duty Fiberglass Single-Phase Horizontal Pin Standoff Bracket with 1″ Nylon Threads

*Representative Image

Features

- Horizontal Position Pin Type Insulator Bracket
- 2″ (heavy duty) fiberglass rod
- 15° Angle
- Base and end fittings are hot dip galvanized ductile iron

General

Catalog Number	1SBH24H2
Description - End Fitting	Horizonal Pin
Material - Threads	Nylon
Strength Rating - Minimum Ultimate, Longitudinal (L)	1200 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1750 lb
UPC	096359588078

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	24 in
Length	24 in
Mounting Bolt Spacing	• 8 in • 10 in
Weight	9.8 lb

Electrical Ratings

Phase	1-Phase

Logistics

Standard Package	1

Product Assets

Catalog Page - CHANCE® Fiberglass Construction Products
Sales Drawings - SA1SBHXXHX
Specifications - 1SBH24H2

©2024 Hubbell Incorporated. All rights reserved