Horizontal Pin Standoff Bracket, 27″

By Chance
Catalog # 1SBH27H2

27″ Heavy Duty Fiberglass Single-Phase Horizontal Pin Standoff Bracket with 1″ Nylon Threads

*Representative Image

Features

- Horizontal Position Pin Type Insulator Bracket
- 2″ (heavy duty) fiberglass rod
- 15° Angle
- Base and end fittings are hot dip galvanized ductile iron

General

Catalog Number	1SBH27H2
Description - End Fitting	Horizonal Pin
Material - Threads	Nylon
Strength Rating - Minimum Ultimate, Longitudinal (L)	1050 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1550 lb
UPC	096359747819

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	27 in
Length	27 in
Mounting Bolt Spacing	• 8 in • 10 in
Weight	10.4 lb

Electrical Ratings

Phase	1-Phase

Logistics

Carton Quantity	2
Pallet Quantity	40
Standard Package	1

Product Assets

Catalog Page - CHANCE® Fiberglass Construction Products
Sales Drawings - SA1SBHXXHX
Specifications - 1SBH27H2

©2024 Hubbell Incorporated. All rights reserved