Vertical Pin Standoff Bracket, 18" w/ Plastisol

By Chance
Catalog # 1SBM18V1

18" Medium Duty Fiberglass Single-Phase Vertical Pin Standoff Bracket with 1" Plasticol Coated Threads

*Representative Image

Features

- Vertical Position Pin Type Insulator Bracket
- 1.5" (medium duty) fiberglass rod
- 15° Angle
- Base and end fittings are hot dip galvanized ductile iron

General

Catalog Number	1SBM18V1
Description - End Fitting	Vertical Pin
Material - Threads	Plastisol
Strength Rating - Minimum Ultimate, Longitudinal (L)	950 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359067801

Dimensions

Diameter - Rod / Tube	1.5 in
Dimensions	18 in x 2.44 in x 1.41 in
Distance From Pole	18 in
Height	1.41 in
Length	18 in
Mounting Bolt Spacing	• 6 in • 8 in
Weight	8.29 lb
Width	2.44 in

Electrical Ratings

Phase	1-Phase

Logistics

Pallet Quantity	120
Standard Package	6

Product Assets

Catalog Page - CHANCE® Fiberglass Construction Products
Catalogs - CHANCE® Fiberglass Construction Products
Sales Drawings - 1-1/2" Vertical Pin Standoff
Specifications - 1SBM18V1

©2024 Hubbell Incorporated. All rights reserved