MF TYPE CURVED LOCK NUT, 3/8in THREAD

By CHANCE Utility
Catalog # 3510

Used with regular square nuts to create a vibration resistant fit. When the MF lock nut contacts the reqular nut, turn an additional 1/2 to 3/4's turn with wrench to firmly lock in place.

*Representative Image

Features

- For 3/8" diameter bolt, tapped 3/8-16-UNC
- Hot dip galvanized per ASTM A-153
- RUS listed, ek - Locknut.

General

Coating	Galvanized, ASTM A-153
Material	Steel
UPC	096359070207

Dimensions

Distance From Pole	N/A
Weight	0.01 lb

Certifications and Compliance

RUS Listed Reference	ek - Locknut

Product Assets

Catalogs - Communications Catalog (CA12042E)
Catalogs - Pole Line Hardware
Sales Drawings - MF Lockout (SA3510)

Related Products

8636 - CARRIAGE BOLT, 3/8in x 6in, 4,250 RATED TENSILE STRENGTH
8604 - BOLT, MACHINE, SQ HEAD, 3/8in x 4in
PS6801 - WASHER, ROUND, 7/16in HOLE, 1in DIA.
C2050188 - SPRING WASHER, REGULAR-DUTY DOUBLE-COIL, 3/8in SIZE

©2023 Hubbell Incorporated. All rights reserved.
CH-3510-SPEC-EN | REV 4/2023