Guy Clamp, 3-Bolt, 5/16in to 1/2in Strand Size

By Chance
Catalog # 6461

Parallel grooves of clamp body tightly traps strand to form a loop type guy deadend.

Features

- Three 5/8″ dia. clamping bolts
- 1-21/32″ x 6″ clamping plates
- Galvanized steel per ASTM A-153
- RUS Listed, u - Deadend for steel or aluminum clad strand

General

Catalog Number	6461
Coating	Galvanized, ASTM A-153
Material	Steel
Type	Guy Deadend
UPC	096359073260

Dimensions

Dimensions	6.000 in x 1.688 in x 2.813 in
Distance From Pole	N/A
Height	2.813 in
Length	6 in
Weight	2.4 lb
Width	1.688 in

Certifications And Compliance

Industry Standard(s)	NEMA PH 23
RUS Listed Reference	u - Deadend for steel or aluminum clad strand

Logistics

Pallet Quantity	960

Product Assets

Catalogs - Communications Catalog
Catalogs - Pole Line Hardware
Installation Manuals - CHANCE® Guy Clamp Instructions
Sales Drawings - Heavy Type Guy Clamp
Specifications - 6461

©2024 Hubbell Incorporated. All rights reserved