1.75″ Square Shaft Helical Extension (SS175), 14/14/14 x 10ft

By Chance
Catalog # C1100476

SS175, 123″ long with 14″,14″,14″ helices.

Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

Application

Helical Anchoring

General

Catalog Number	C1100476
Coating	Galvanized
Finish Type	Galvanized
Number of Helices	3
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	100000 lb.
Torque Rating	10500 ft-lbs
Type	Anchor Extensions
UPC	096359009832

Dimensions

Anchor Helix Diameter(s)	14 in - 14 in - 14 in
Length	120 in
Weight	167.58 lb

Logistics

Pallet Quantity	12 EA
Standard Package	1

Product Assets

Catalogs - Anchors
Installation Manuals - Chance Helical Pile/Anchor Installation Log Form to record installation details of Chance helical piles.
Installation Manuals - TD06132E_Type_SS_and_RR_Anchors
Literature - New Construction Helical Pile Foundation System
Literature - CHANCE Anchor Tool Inspection and Maintenance
Literature - Square Shaft Efficient Helical Pile Design
Literature - Anchoring
Sales Drawings - SS175 Anchors
SDS - MSDS - Galvanized Steel Products
Specifications - C1100476
Video - CHANCE Square Shaft Anchor Installation
Video - CHANCE Square Shaft Anchor Tools Selection Process

©2024 Hubbell Incorporated. All rights reserved