Anchor, Disk Rod, 1-1/4in X 15ft Tripleye

By Chance
Catalog # C2000140

*Representative Image

Corrosion-Resistant Disk Anchor Protected Rod 1.25" (31.75 mm) Diameter Rod, 15' (4572 mm) long with Tripleye. Cap Nut and fiber washer is attached.

Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading,kinking, or bending.
- Hot dipped galvanized per ASTM A153, Black asphalt paint applied over galvanizing, plastic tube assembled on rod
- Includes Fiber Washer and Cap nut
- Rods used with round Disk Anchors

Application

Earth Tension Anchoring

General

Catalog Number	C2000140
Coating	Galvanized, ASTM A-153, Black Paint, Plastic Tube
Eyenut Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	58000 lb.
Type	Corrosion-Resistant Anchor Parts
UPC	096359622840

Dimensions

Length	180 in
Rod Diameter	1.25 in
Weight	75 lb

Logistics

Standard Package	1

Product Assets

Catalogs - Appendix A - Transmission And Substation Technical Design Manual
Installation Manuals - TD06134E_Corrosion_Protected_ Disk_ Anchors
Literature - Anchoring
Sales Drawings - 30 Inch Diameter Disk Anchor With 15 FT X 1-1/4 Inch 2 Pcs Rod
Specifications - C2000140

©2024 Hubbell Incorporated. All rights reserved