Anchor, Tool, Kelly Bar Adapter, 2.625in Hex, 15,000 ft-lb rating

By Chance
Catalog # C3030937

Anchor, Tool, Kelly Bar Adapter, 2.625in Hex, 15,000 ft-lb rating

*Representative Image

Features

- Kelly Bar Adapter attaches to truck's torque motor drive shaft (Kelly Bar)
- Kelly bar adapter has twelve holes for 5/8″ bolts on a 7-5/8″ bolt circle, comes with twelve 5/8″ Grade 5 bolts, nuts & lockwashers and bent arm pin with coil lock
- Painted with green paint

Application

Anchor/Pile Installation

General

Bolt Grade	5
Catalog Number	C3030937
Coating	Painted
Kelly Bar Shape	Hex
Number of Bolt Holes	12
Torque Rating	15000 ft-lbs
Type	Anchor/Pile Installation Tools
UPC	096359015307

Dimensions

Anchor Installation Hole Size	0.625 in
Diameter - Bolt	0.625 in
Diameter - Bolt Circle	7.625 in
Dimensions	8.25 in x 10.500 in x 9.500 in
Height	9.5 in
Kelly Bar Adapter Inside Width	2.625 in
Kelly Bar Hole Distance to Flange	4.25 in
Length	8.25 in
Weight	25.48 lb
Width	10.5 in

Logistics

Pallet Quantity	36
Standard Package	1

Product Assets

Catalogs - Anchor Tools
Installation Manuals - Instructions for CHANCE Kelly Bar Adapters
Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide
Literature - CHANCE Anchor Tool Inspection and Maintenance
Literature - Anchoring
Sales Drawings - Tough One Wrench System
Specifications - C3030937
Video - CHANCE Pisa Drive Tools

©2024 Hubbell Incorporated. All rights reserved