









## Duplex Receptacle Wallplates

Description	Color	Thermoplastic			Material	Metal Catalog Number
		Standard	Mid-Size	Jumbo		
1-Gang, 1-Duplex 	Black	<b>P8BK</b>	<b>PJ8BK</b>	-	Aluminum	<b>SA8</b>
	Blue	-	<b>PJ8BL</b>	-	Brass	<b>SB8</b>
	Brown	<b>P8</b>	<b>PJ8</b>	-	Brass Plated	<b>SBP8</b>
	Gray	<b>P8GY</b>	<b>PJ8GY</b>	-	Chrome	<b>SCH8</b>
	Ivory	<b>P8I</b>	<b>PJ8I</b>	<b>NPJJ8I</b>	S/S 302/304	<b>SS8</b>
	Light Almond	<b>P8LA</b>	<b>PJ8LA</b>	<b>NPJJ8LA</b>	S/S 430	<b>SS8L</b>
	Orange	<b>P8OR</b>	-	-		
	Red	<b>P8R</b>	<b>PJ8R</b>	-		
	White	<b>P8W</b>	<b>PJ8W</b>	<b>NPJJ8W</b>		
2-Gang, 2-Duplex 	Black	<b>P82BK</b>	<b>PJ82BK</b>	-	Aluminum	<b>SA82</b>
	Brown	<b>P82</b>	-	-	Brass	<b>SB82</b>
	Gray	<b>P82GY</b>	<b>PJ82GY</b>	-	Brass Plated	<b>SBP82</b>
	Ivory	<b>P82I</b>	<b>PJ82I</b>	-	Chrome	<b>SCH82</b>
	Light Almond	<b>P82LA</b>	<b>PJ82LA</b>	-	S/S 302/304	<b>SS82</b>
	Orange	<b>P82OR</b>	-	-	S/S 430	<b>SS82L</b>
	Red	<b>P82R</b>	<b>PJ82R</b>	-		
	White	<b>P82W</b>	<b>PJ82W</b>	-		
	3-Gang, 3-Duplex 	Ivory	<b>P83I</b>	-	-	Aluminum
White		<b>P83W</b>	-	-	Brass	⓪
4-Gang, 4-Duplex 					Brass Plated	⓪
					Chrome	⓪
					S/S 302/304	<b>SS84</b>
					S/S 430	-
2-Gang, 1-Duplex 					Brass	-
					Brass Plated	-
					Chrome	-
					S/S 302/304	<b>SS748</b>
					S/S 430	-

## Single 15/20A Straight Blade or 15A Twist-Lock® Receptacle Wallplates

Description	Color	Thermoplastic			Material	Metal Catalog Number
		Standard	Mid-Size	Jumbo		
1-Gang, 1-Single 1.40 in. (35.6) Dia. Hole 	Black	<b>P7BK</b>	-	-	Aluminum	<b>SA7</b>
	Brown	<b>P7</b>	-	-	Brass	<b>SB7</b>
	Gray	<b>P7GY</b>	-	-	Brass Plated	<b>SBP7</b>
	Ivory	<b>P7I</b>	<b>PJ7I</b>	-	Chrome	<b>SCH7</b>
	Light Almond	<b>P7LA</b>	<b>PJ7LA</b>	-	S/S 302/304	<b>SS7</b>
	Red	<b>P7R</b>	-	-	S/S 430	<b>SS7L</b>
	White	<b>P7W</b>	<b>PJ7W</b>	-		
2-Gang, 1-Single 1.40 in. (35.6) Dia. Hole 					Aluminum	-
					Brass	-
					Brass Plated	-
					Chrome	-
					S/S 302/304	<b>SS747</b>
					S/S 430	-
2-Gang, 2-Single 1.40 in. (35.6) Dia. Hole 					Aluminum	⓪
					Brass	⓪
					Brass Plated	⓪
					Chrome	⓪
					S/S 302/304	<b>SS72</b>
					S/S 430	-

Note: Thermoplastic wallplates feature pre-inserted captive screws for faster assembly in single gang configurations.

⓪ Available as a custom wallplate, see pages N-32 to N-34. Consult custom wallplates section for additional openings and combinations.

Dimensions in Inches (mm)