


Plates for Use in SystemOne 4/5 & 8*/10-Gang Floor Boxes

- UL 514A listed

Cat. No.	Plate Style	Cat. No.	Plate Style
FB10MPREC ①	(1) Decorator Opening	FB10MPDUP ②	(1) Duplex Opening
FB10MPBNK	1-Gang Blank Plate	FB10MPKEY	(1) Opening with Hubbell 6-Port Frame for Keystone Jacks Frame for Keystone Jacks
FB10MPTRAC	(2) Openings for (6) Ortronics TracJack®	FB10MPFT	Cable Feed Through with Bushing
Cat. No	Two Gang Plate Style	Cat. No	Two Gang Plate Style
FB10MP2A ③	Decorator Openings	FB10MP2E ④	Duplex Openings
FB10TLX	(1) Simplex Opening 1.40 in. Diameter	FB10TLA	(1) Twist-Lock® Opening 1.60 in. Diameter
FB10MP2B	(6) 1U Hubbell iStation Modules	FB10MPMAAP	Siemon CT Series
FB10MPAAP	(4) Extron® AAP Openings		
Cat. No	Three Gang Plate Style	Cat. No	Three Gang Plate Style
FB10TLY	(2) Simplex Opening 1.40 in. Diameter	FB10TLB	(3) Twist-Lock® Opening 1.60 in. Diameter
FB10MP3GAPP ⑤	(1) Opening for Appliance Receptacle, requires 2-Gang industry plate for trim out		
Cat. No	Five Gang Plate Style	Cat. No	Five Gang Plate Style
FB10TLC	(3) Simplex Opening 1.40 in. Diameter	FB10TLZ	Twist-Lock® Opening 1.60 in. Diameter
FB10MPNEMA2XG ⑥	(2) 2-Gang. Meets NEMA Spacing. Ideal for Crestron® DM –TX Product and Power. Ships with Low Voltage Divider.	FB10MPNEMA4G ⑦	(4) Single Service Openings Utilizing NEMA Wallplate. (No Low Voltage Divider Option)


Note: *Use with FB10MPNEMA2XG and/or FB10MPNEMA4G for 8-gang configuration.



Pre-Wired Device Plates


- Reduces wiring and installation times
- 8 inch stranded leads mounted to the face plate

Description	Type	20A
Duplex, Gray.	Standard Tamper-Resistant	PWFB10MPCR20GRY ⑧ PWFB10MPCR20GRYTR
Decorator, Gray.	Standard Tamper-Resistant	PWFB10MPDR20GRY ⑨ PWFB10MPDR20GRYTR



Accessories

Description		Catalog Number
(1) 2" threaded zinc hub for use with CFB45G55 and CFB10G55 series floor boxes; replaces CFBKOPLATE .		CFBHUB2
(2) 1-1/4" PVC hubs with reducers for use with CFB45G55 and CFB10G55 series floor boxes; replaces CFBKOPLATE . Reducers include: (2) 1" reducer, (2) 3/4" reducers, and (2) 1/2" Reducer/Plugs.		CFBHUB125PVC
(2) 2" PVC hubs with reducers for use with CFB45G55 and CFB10G55 series floor boxes; replaces CFBKOPLATE . Reducers include: (2) 1-1/2" reducers, (2) 1-1/4" reducers, and (2) 1" Reducer/Plugs.		CFBHU200PVC ⑩
Replacement knock-out plates.	Standard Epoxy Coating	CFBKOLATE CFBKOPATECR
ETERNAL™ Replacement Round Cover Adapter, 10-gang Floor Box		CFB4510GS1R8ADAPTE
Stackable ring to increase box height and concrete pour depth by 3/4 in. increments above top plane of floor box. One ring per 3/4 in. depth increase. Must be installed before concrete pour.		CFB8RCVRR075
Finished floor height adjustment ring - increase post pour adjustment ; use with round cover series.	0 - 1/4 in. 1/4 in. - 1/2 in. 1/2 in. - 3/4 in.	CFB8RCVRR1* CFB8RCVRR2 ⑪ CFB8RCVRR3
Rectangular pre-pour 1/2 in. extension caps (2 pack).		610GEXTENDCAP2PK ⑫
Replacement temporary rectangular steel and yellow concrete pre-pour covers		610GTEMPCVR
Replacement spacer around wire-way.		FB10MPX
Replacement divider.		FB4510GDIV



Note: *Included with standard **CFB45G55R** and **CFB10G55R** series floor boxes.

Extron® is a registered trademark of Extron Electronics. Crestron® is a registered trademark of Crestron Electronics, Inc. FSR® is a registered trademark of FSR Inc. TracJack®, Series II® and Ortronics® are registered trademarks of Ortronics/Legrand.

Dimensions in Inches (mm)