CHANCE®

15 kV, 110 kV BIL, Type C Linkbreak Porcelain Cutout w/100A 16kAIC fuseholder

By Chance
Catalog # C720114ED

15 kV, 110 kV BIL, Linkbreak Type C Porcelain Cutout with a 100A, 16kAIC fuseholder, small eyebolt connector and a D-shape pole mounting bracket.

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 – 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	D-shape for pole mounting
Catalog Number	C720114ED
Description - Replacement Fuse Holder	T720-114T
Type	Cutout

Dimensions

Weight	25.73 lb

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	8.7" (220mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient
Voltage Rating	15 kV

Logistics

Pallet Quantity	72 EA
Standard Package	1

Product Assets

Catalogs - Type C-Porcelain Cutouts
Installation Manuals - Link Break Cutout Installation Instructions
Literature - Switching Line Card_FAQ_2019
Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING
Sales Drawings - Cutout, Linkbreak 110 KV BIL
Specifications - C720114ED
Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality
Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience

©2024 Hubbell Incorporated. All rights reserved