









Duplex Receptacle Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Nylon Jumbo	Material	Metal Catalog Number
 1-Gang, 1-Duplex	Black	NP8BK	NPJ8BK	-	Aluminum	SA8
	Blue	-	NPJ8BL	-	Brass	SB8
	Brown	NP8	NPJ8	-	Brass Plated	SBP8
	Gray	NP8GY	NPJ8GY	-	Chrome	SCH8
	Ivory	NP8I	NPJ8I	NPJJ8I	S/S 302/304	SS8
	Light Almond	NP8LA	NPJ8LA	NPJJ8LA	S/S 430	SS8L
	Office White	NP8OW	NPJ8OW	-		
	Orange	NP8OR	-	-		
	Red	NP8R	NPJ8R	-		
	White	NP8W	NPJ8W	NPJJ8W		
 2-Gang, 2-Duplex	Black	NP82BK	NPJ82BK	-	Aluminum	SA82
	Brown	NP82	NPJ82	-	Brass	SB82
	Gray	NP82GY	NPJ82GY	-	Brass Plated	SBP82
	Ivory	NP82I	NPJ82I	-	Chrome	SCH82
	Light Almond	NP82LA	NPJ82LA	-	S/S 302/304	SS82
	Office White	NP82OW	NPJ82OW	-	S/S 430	SS82L
	Orange	NP82OR	-	-		
	Red	NP82R	NPJ82R	-		
	White	NP82W	NPJ82W	-		
	 3-Gang, 3-Duplex	Brown	NP83	-	-	Aluminum
Ivory		NP83I	-	-	Brass	①
White		NP83W	-	-	Brass Plated	①
					Chrome	①
 4-Gang, 4-Duplex	Brown	NP84	-	-	S/S 302/304	SS84
	Ivory	NP84I	-	-	S/S 430	-
	White	NP84W	-	-		
 2-Gang, 1-Duplex	Brown	-	-	-	Brass	-
	Ivory	-	-	-	Brass Plated	-
	White	-	-	-	Chrome	-
					S/S 302/304	SS748
				S/S 430	-	

Single 15/20A Straight Blade or 15A Twist-Lock® Receptacle Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Nylon Jumbo	Material	Metal Catalog Number	
 1-Gang, 1-Single 1.40 in. (35.6) Dia. Hole	Black	NP7BK	NPJ7BK	-	Aluminum	SA7	
	Brown	NP7	NPJ7	-	Brass	SB7	
	Gray	NP7GY	NPJ7GY	-	Brass Plated	SBP7	
	Ivory	NP7I	NPJ7I	-	Chrome	SCH7	
	Light Almond	NP7LA	NPJ7LA	-	S/S 302/304	SS7	
	Office White	NP7OW	NPJ7OW	-	S/S 430	SS7L	
	Red	NP7R	NPJ7R	-			
	White	NP7W	NPJ7W	-			
	 2-Gang, 1-Single 1.40 in. (35.6) Dia. Hole	Brown	-	-	-	Aluminum	-
		Ivory	-	-	-	Brass	-
White		-	-	-	Brass Plated	-	
					Chrome	-	
					S/S 302/304	SS747	
 2-Gang, 2-Single 1.40 in. (35.6) Dia. Hole	Brown	-	-	-	Aluminum	①	
	Ivory	-	-	-	Brass	①	
	White	-	-	-	Brass Plated	①	
					Chrome	①	
					S/S 302/304	SS72	
				S/S 430	-		

Note: All nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

① Available as a custom wallplate, see pages O-32 to O-35. Consult custom wallplates section for additional openings and combinations.

Dimensions in Inches (mm)