

## Painted Pedestal FRPT 2 and 3 Inch Core Hole Units, for Use In Concrete Floors

### 3 Inch Core Hole, Two-Piece Unit

Description	Catalog Number
Large Capacity Multi-Service Pedestal Through-Floor Fitting with (1) 1 1/4 in. EMT stem for low voltage and (1) 1/2 in. EMT stem for power applications.	<b>PT7XC</b>
Specifications:	
<ul style="list-style-type: none"> <li>• 1 – 4 hour fire rating (1 – 3 hour for steel floor units and concrete topping, D900 Series Design)</li> <li>• For 2 1/4 in. to 7 in. floor thickness</li> <li>• Approved for use in the City of Chicago</li> </ul>	






### 2 Inch Core Hole, Two-Piece Unit

Description	Catalog Number
Multi-Service Pedestal Through-Floor Fitting with (1) 3/4 in. EMT stem for low voltage and (1) 1/2 in. EMT stem for power applications.	<b>PT27A</b>
Specifications:	
<ul style="list-style-type: none"> <li>• 1 – 4 hour fire rating (1 – 3 hour for steel floor units and concrete topping, D900 Series Design)</li> <li>• For 2 1/4 in. to 7 in. floor thickness</li> <li>• Approved for use in the City of Chicago</li> </ul>	



Note: See page P-45 for technical information.

## Pedestal Service Fittings (Order 1 plate per gang)

Description	Color/Material	Catalog Number	Description	Color	Catalog Number	Description	Color	Catalog Number
2-Gang	Alum. Finish Black Gray	<b>FR280ALA</b> <b>FR280BKA</b> <b>FR280GYA</b>	4-Gang	Black Gray	<b>FR480BKA</b> <b>FR480GYA</b>	6-Gang	Black Gray	<b>FR680BKA</b> <b>FR680GYA</b>
Use with PT27A only.			Use with PT27A or PT7XC.			Use with PT27A or PT7XC.		
		<b>FR280BKA</b>			<b>FR480GYA</b>			<b>FR680BKA</b>

- Painted aluminum housing with low voltage barrier(s); plates and devices sold separately
- For additional barriers, use **FRBR1**, see page P-33.
- UL Listed and CSA Certified

Note: See page P-45 for technical information.

## Pedestal Face Plates (Order 1 plate per gang)

Description	Color/Material	Catalog Number	Description	Color/Material	Catalog Number
Duplex	Black Gray	<b>SS2309DBKA</b> <b>SS2309DGYA</b>	Furniture feed (3/4 in. KO)	Alum. Finish Black Gray	<b>SS2309FALA</b> <b>SS2309FBKA</b> <b>SS2309FGYA</b>
Style Line®/GFCI	Black Gray	<b>SS2309SLBKA</b> <b>SS2309SLGYA</b>	Furniture feed (1 in. KO)	Black Gray	<b>SS2309F1BKA</b> <b>SS2309F1GYA</b>
Single receptacle (1.39 in. OD)	Black Gray	<b>SS2309SBKA</b> <b>SS2309SGYA</b>	Bushed data opening (1 in. ID)	Black Gray	<b>SS2309TBKA</b> <b>SS2309TGYA</b>
Blank	Alum. Finish Black Gray	<b>SS2309BALA</b> <b>SS2309BBKA</b> <b>SS2309BGYA</b>			

- Painted aluminum plates
- UL Listed and CSA Certified