CHANCE®

1 A, Type STH fuselinks, 23″ Length, Removable Head

By Chance
Catalog # M1STHA23

1 amp, Type STH Cutout fuselink with a 23″ (584.2mm) pigtail and a removable buttonhead.

Features

- Comparable to S&C Standard Speed fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Catalog Number	M1STHA23
Fuse Head Style	Removable
Fuselink Type	Type STH
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359630920

Dimensions

Length - Fuselink	23″ (584.2mm)

Electrical Ratings

Amperage Rating	1 A

Logistics

Carton Quantity	200
Pallet Quantity	4832
Standard Package	10

Product Assets

Catalogs - Fuse Links
Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type STH
Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type STH
Literature - Switching Line Card_FAQ_2019
Sales Drawings - Type Standard Fuse Links, Solid & Removable Head
Specifications - M1STHA23
Test Documents - STH Total Clear
Test Documents - STH Min Melt

©2024 Hubbell Incorporated. All rights reserved