CHANCE®

50 A, Type QH Fuselinks, 23" Length, Solid Head

By Chance
Catalog # M50QH23

50 amp, Type QH Cutout fuselink with a 23" (584.2mm) pigtail.

Features

- Comparable to Cooper/Kearney Type QA fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Catalog Number	M50QH23
Fuse Head Style	Solid
Fuselink Type	Type QH
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359631880

Dimensions

Length - Fuselink	23" (584.2mm)

Electrical Ratings

Amperage Rating	50 A

Logistics

Pallet Quantity	4800
Standard Package	10

Product Assets

Catalogs - Fuse Links
Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type QH
Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type QH
Literature - Switching Line Card_FAQ_2019
Sales Drawings - Type QH Fuse Links, Solid & Removable Head
Specifications - M50QH23
Test Documents - QH Min Melt
Test Documents - QH Total Clear

©2024 Hubbell Incorporated. All rights reserved