

Non-Metallic Raceway



Non-Metallic PlugTrak®

Available in Standard, Isolated Ground (IG), Tamper-Resistant (TR) and USB (U) versions.



	Amp Circuits	Duplex Recept. Ports	USB Recept. Ports	Recept. Spacing (in.)	Color		
					Black	White	Office White
5 Foot Base and Cover	15 Single	5	—	12	PT155112BK	PT155112W	PT155112
	15 Two	5	—	12	PT155212BK	PT155212W	PT155212
	15 Single	4	—	15	PT155115BK	PT155115W	PT155115
	15 Single	2	—	30	PT155130BK	PT155130W	PT155130
	15 TR/Single	5	—	12	PT155112TRBK	PT155112TRW	PT155112TR
	20 Single	5	—	12	PT205112BK	PT205112W	PT205112
	20 Two	5	—	12	PT205212BK	PT205212W	PT205212
	20 Single	4	—	15	PT205115BK	PT205115W	PT205115
	20 Two	4	—	15	PT205215BK	PT205215W	PT205215
	20 Single	2	—	30	PT205130BK	PT205130W	PT205130
	20 TR/Single	5	—	12	PT205112TRBK	PT205112TRW	PT205112TR
	6 Foot Base and Cover	15 Single	6	—	12	PT156112BK	PT156112W
15 Two		6	—	12	PT156212BK	PT156212W	PT156212
15 Single		4	—	18	PT156118BK	PT156118W	PT156118
15 Single		3	—	24	PT156124BK	PT156124W	PT156124
15 USB/Single		4	4	12	PT156112UBK	PT156112UW	PT156112U
20 Single		9	—	8	PT206108BK	PT206108W	PT206108
20 Two		9	—	8	PT206208BK	PT206208W	PT206208
20 Single		6	—	12	PT206112BK	PT206112W	PT206112
20 Two		6	—	12	PT206212BK	PT206212W	PT206212
20 Single		4	—	18	PT206118BK	PT206118W	PT206118
20 Two		4	—	18	PT206218BK	PT206218W	PT206218
20 Single		3	—	24	PT206124BK	PT206124W	PT206124
20 Two	3	—	24	PT206224BK	PT206224W	PT206224	
20 Single	2	—	36	PT206136BK	PT206136W	PT206136	

Note: Each Non-Metallic PlugTrak is supplied with one PL1EC end cap and "IG" stickers for isolated ground applications.



	Length (ft.)	Cord Length (ft.)	Duplex Recept. Ports	USB Recept. Ports	Color			
					Black	White	Office White	
Portable	15	3	6	3	—	PT153112PBK	PT153112PW	PT153112P
	15	5	6	5	—	PT155112PBK	PT155112PW	PT155112P
	15	3	6	4	2	PT153112UPBK	PT153112UPW	PT153112UP
	20	3	6	2	—	PT203112PBK	PT203112PW	PT203112P
	20	5	6	5	—	PT205112PBK	PT205112PW	PT205112P
Supporting Mounting Clip for Portable PlugTrak.							PL1MC	

Note: Includes ON/OFF switch and circuit breaker.

	Descript.	Catalog No.	Descript.	Catalog No.
Device Boxes	1-Gang Low Profile	PDB12LP	1-Gang Deep	PDB12D
	1-Gang Standard	PDB12S	Round Lighting Fixture	PDB12LF
	2-Gang Deep Undivided	PDB12TGLV	2-Gang Deep Divided	PDB12TGD
Fittings	Internal Elbow Base and Cover	PL1IEBC	Internal Elbow Cover Only	PL1IE
	External Elbow Base and Cover	PL1EEBC	External Elbow Cover Only	PL1EE
	Flat Elbow Base and Cover	PL1FEBC	Flat Elbow Cover Only	PL1FE
	Tee Base and Cover	PL1TCBC	Tee Cover Only	PL1TC
	Splice Cover	PL1SC	Safety Strap	PL1SS
	Conduit Adapter/Ceiling Fitting	PT12CA	Conduit Adapter/Ceiling Fitting	PLP1CACF
	End Cap	PL1EC		

Note: For additional colors add "BK" for Black or "W" for white. See page S-56 for additional information.