Barry D.E.W. Line® Rescue Rope, 50 ft/15.2 m

By Chance
Catalog # PSCDEWNF34050

High angle rescue rope tool for evacuation of workers performing live line work on AC or DC systems.

Features

- Rated Working Load 500 lb./226.7 kg
- Meets or exceeds dry or wet electrical requirements of IEC 62196:2009 and ASTM F1701-12
- Cleanable and easy to maintain and test
- Arc-Flash Category 4 rated
- Fixed length with plastic thimbles and sealed terminations
- Storage bag with dessicant optional

General

Catalog Number	PSCDEWNF34050
UPC	096359752981
Working Load Limit	500 lb
Working Load Limit Metric	226 kg

Dimensions

Diameter	0.5 in
Diameter - Metric	12 mm
Length	50 ft
Length Metric	15.2 m
Weight	7.3 lb
WeightMetric	3.3 kg

Product Assets

Installation Manuals - Barry D.E.W. Line Insulating Rope Equipment
Literature - CHANCE® Barry D.E.W. Line® Rethink Rope
Specifications - PSCDEWNF34050

©2024 Hubbell Incorporated. All rights reserved